

Warranty

Arlec guarantees this product in accordance with the Australian Consumer Law and all other applicable Australian and New Zealand laws that are unable to be excluded.

Arlec also warrants to the original first purchaser of this product ("you") from a retailer with which this document is given that this product will be free of defects in materials and workmanship for a period of 12 months from the date of purchase; provided the product is not used other than for the purpose, or in a manner not within the scope of the recommendations and limitations, specified by Arlec, is new and not damaged at the time of purchase, has been maintained in accordance with the recommendations specified by Arlec, has not been subjected to abuse, misuse, neglect or damage, has not been modified or repaired without the approval of Arlec and has not been used for commercial purposes ("Warranty").

If you wish to claim on the Warranty, you must, at your own expense, return the product, and provide proof of original purchase and your name, address and telephone number, to Arlec at the address below or the retailer from whom you originally purchased the product within 12 months from the date of purchase.

Arlec will (or authorise the retailer to) assess any claim you may make on the Warranty in the above manner and if, in Arlec's reasonable opinion, the Warranty applies, Arlec will at its own option and expense (or authorise the retailer to) replace the product with the same or similar product or repair the product and return it to you or refund the price you paid for the product. Arlec will bear its own expenses of doing those things, and you must bear any other expenses of claiming on the Warranty.

ARLEC

Arlec's telephone number, address and email address for purposes of giving the Warranty are:

Telephone Number: 1800 826 859 (in Australia)
0800 003 329 (in New Zealand)

Street Address: Caribbean Park, 36 Lakeview Drive, Scoresby, VIC 3179, Australia

Postal Address: PO Box 2596, Rowville, VIC 3178, Australia

Email: cs@arlec.com.au

For goods purchased in Australia (only):

The Warranty is in addition to other rights and remedies you may have under a law in relation to the product to which the Warranty relates.

Our goods come with guarantees that cannot be excluded under the Australian Consumer Law. You are entitled to a replacement or refund for a major failure and for compensation for any other reasonably foreseeable loss or damage. You are also entitled to have the goods repaired or replaced if the goods fail to be of acceptable quality and the failure does not amount to a major failure.

For goods purchased in New Zealand (only):

The Warranty is in addition to, and does not affect, other rights and remedies you may have under a law in relation to the product to which the Warranty relates.

Our goods come with guarantees that can only be excluded under the New Zealand Consumer Guarantees Act 1993 to the extent you are acquiring the product for a business purpose and it would be fair and reasonable for Arlec to contract out of those guarantees.

Arlec Australia Pty. Ltd. ACN 009 322 105 gives the Warranty for goods purchased from a retailer in Australia by you and Arlec New Zealand Limited NZBN 9429030738294 gives the Warranty for goods purchased from a retailer in New Zealand by you (collectively Arlec).

CPIN004224/3

OPERATION INSTRUCTIONS

ARLEC

LED MULTI-PURPOSE PORTABLE WORKLIGHT

400 lumens LED

2 x 3W LED Lights

5000K Daylight

360° Beam Angle

WL0027



RECHARGEABLE Lithium Battery



Please read these instructions carefully before use.

Introduction:

The Arlec WL0027 is suitable for indoor use only. It is ideal for contractor, tradesman and DIY handyman applications.

Charging:


1. To charge the battery, insert the USB cable into the USB Type C connector above switch button. The red LED will indicate the progress of charging. When the battery is fully charged, green LED will light up.
2. It takes around 3 hours to be fully charged per worklamp.
3. Operating worklamp with power adapter/car charger is recommended for short-term use. It is suggested that you charge the battery before use.
4. Use only the power adapter/car charger supplied.

Operation:


- To operate the worklight, press the POWER switch button gently on the handle to switch ON and OFF.





- 360 degree beam angle when fully assembled as one light unit.
- Split in to 2 individual lights as inspection worklights.



- It extends illumination when joining two inspection lights together. It can split easily into two lights again by pushing the button on the joint part.



- It has swivel arms with magnetic bases, as well as fold away hanging hooks. These functions allow this worklight to be used under various environment through multi-purpose.



Important Notes:

- The lamp is IP20 rated and is suitable for use indoors only.
- Avoid looking directly at the LED lights.
- Keep out of reach of young children and pets.
- To clean the light, use a clean wring out damp cloth and mild detergent.
- Do not expose the light to extreme temperatures or solvents.
- If not using the lamp for long periods, charge for 1-2 hours before storing.
- The light source inside this luminaire is non-user replaceable type.
- The electrical parts can only be serviced by a qualified tradesman, in compliance with standards/specifications.

Minimum distance from lighted objects 0.3 metres.



The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

This appliance is not intended for use by persons (including children) with reduced physical, sensory or mental capabilities, or lack of experience and knowledge, unless they have been given supervision or instruction concerning use of the appliance by a person responsible for their safety.

Specifications

Light:	2 x 3W LED Lights
Light Output:	200 Lumen per light
Charge Time:	Approx. 3 hours per light
Run Time:	Up to 2 hours when fully charged
Ingress Protection Rating:	IP20
Colour Temperature:	5000K Daylight
CRI:	>80
Weight:	0.68kg