




No-Seep Wax Toilet Bowl Gaskets



See Wholesale Net Catalog Category 3

No-Seep wax gaskets have a polyethylene sleeve permanently molded in a blend of preformed amber petrolatum wax with a melting point of 150-160°F. No-Seep gaskets are molded into plastic trays for added protection and clean efficient handling until installation. Gaskets are available with either 4" x 3" or 4" polyethylene sleeves. All gaskets conform to Federal Specification TT-P-1536A. No-Seep No. 1 and No. 10 gaskets are for 3" and 4" lines. No-Seep No. 5 and No. 50 gaskets are for 4" lines only.

DIRECTIONS FOR USE

1. Be sure No-Seep is at least 21°C. temperature to insure proper flow of wax.
2. Press No-Seep over horn outlet of toilet bowl, extending plastic flange away from the bowl.
3. Set bowl in place and use body weight to compress No-Seep.
4. Twist bowl slightly to spread wax.
5. Tighten flange bolts carefully to prevent breaking the bowl.

CHEMICAL AND PHYSICAL PROPERTIES

Specific Gravity:	0.86
Appearance:	light amber
Odor:	petroleum wax
Flash Point:	550°F
Water Solubility:	insoluble
Freeze/Thaw Cycle:	will not freeze
Gasket Weights:	No-Seep No. 1 160-195 g. No-Seep No. 10 250-285 g. No-Seep No. 5 160-195 g. No-Seep No. 50 250-285 g.



4840 York Blvd | Los Angeles CA 90042 | www.CandLsupply.com
Toll Free: (800) 458-2377 | Fax: (323) 258-6523 | sales@CandLsupply.com

HMIS	
Health	
Flammability	
Reactivity	
Personal Protection	