

Wick Size Chart | 2-3" Containers

DISTRIBUTING

Container Diameter	Ceda Serica	EC-26	CB-2	Soy	Coconut 83
2" - 2.5"	<p>CD 4, 6, 7 CDN 4, 6, 7 LX 12, 14 ECO 2, 4, 6 HPSP 30, 33, 36, 39 Rigid Curl 2.175, 2.275 Ultra Core 1.651, 1.705 AL 80, 100, 110 ZINC 36-24-24; 44-20-18; 44-24-18 Premier 715, 720, 725, 730, 735, 740 Superior 800, 810, 820 HELIX 3, 5, 7.5 P Series 140/2-30, 160/2-30</p>	<p>CD 4, 6, 7 CDN 4, 6, 7 LX 12, 14 ECO 2, 4, 6 HPSP 30, 33, 36, 39 Rigid Curl 2.175, 2.275 Ultra Core 1.651, 1.705 AL 80, 100, 110 ZINC 36-24-24; 44-20-18; 44-24-18 Premier 715, 720, 725, 730, 735, 740 Superior 800, 810, 820 HELIX 3, 5, 7.5 P Series 120/2-26</p>	<p>CD 4, 6, 7 CDN 4, 6, 7 LX 12, 14 ECO 2, 4, 6 HPSP 30, 33, 36, 39 Rigid Curl 2.175, 2.275 Ultra Core 1.651, 1.705 AL 80, 100, 110 ZINC 36-24-24; 44-20-18; 44-24-18 Premier 715, 720, 725, 730, 735, 740 Superior 800, 810, 820 HELIX 3, 5, 7.5 P Series 120/2-26, 140/2-30</p>	<p>CD 2, 3, 4 CDN 2, 3, 4 LX 8, 10 ECO 1, 1.5, 2 HPSP 24, 27, 30, 33, 36 Rigid Curl 2.069 Ultra Core 1.450, 1.600 AL 80, 100 ZINC 36-24-24; 44-20-18 Premier 705, 710, 715, 720 Superior 800, 810 HELIX 1, 3, 5 P Series 120/2-26, 140/2-30</p>	<p>CD 2, 3, 4 CDN 2, 3, 4 LX 8, 10 ECO 1, 1.5, 2 HPSP 24, 27, 30, 33, 36 Rigid Curl 2.069 Ultra Core 1.450, 1.600 AL 80, 100 ZINC 36-24-24; 44-20-18 Premier 705, 710, 715, 720 Superior 800, 810 HELIX 1, 3, 5 P Series 120/2-26, 140/2-30</p>
2.5"-2.8"	<p>CD 7, 8, 10 CDN 7, 8, 10 LX 16, 18 ECO 4, 6 HPSP 42, 45, 48, 51, 54 Rigid Curl 2.275, 2.486 Ultra Core 1.792, 1.832 AL 110, 120, 140 ZINC 44-24-18; 44-28-18; 51-32-18 Premier 735, 740, 750 Superior 830, 840 HELIX 5, 7.5, 10 P Series 180/2-35, 180/2-35, 180/4-35</p>	<p>CD 7, 8, 10 CDN 7, 8, 10 LX 16, 18 ECO 4, 6 HPSP 42, 45 Rigid Curl 2.275, 2.486 Ultra Core 1.792, 1.832 AL 110, 120, 140 ZINC 44-24-18; 44-28-18; 51-32-18 Premier 735, 740, 750 Superior 830, 840 HELIX 5, 7.5, 10 P Series 140/2-30, 160/2-30, 180/2-35, 180/4-35</p>	<p>CD 7, 8, 10 CDN 7, 8, 10 LX 16, 18 ECO 4, 6 HPSP 36, 39, 42, 45 Rigid Curl 2.275, 2.486 Ultra Core 1.792, 1.832 AL 110, 120, 140 ZINC 44-24-18; 44-28-18; 51-32-18 Premier 735, 740, 750 Superior 830, 840 HELIX 5, 7.5, 10 P Series 140/2-30, 160/2-30, 180/2-35, 180/4-35</p>	<p>CD 4, 5, 6 CDN 4, 5, 6 LX 12, 14 ECO 4, 6, 8 HPSP 39, 42, 45 Rigid Curl 2.069, 2.175 Ultra Core 1.600, 1.651, 1.705 AL 110, 120 ZINC 44-24-18; 44-28-18 Premier 720, 725, 730, 735 Superior 810, 820 HELIX 3, 5, 7.5 P Series 160/2-30, 180/2-35, 180/4-35</p>	<p>CD 4, 5, 6 CDN 4, 5, 6 LX 12, 14 ECO 4, 6, 8 HPSP 30, 33, 36, 39 Rigid Curl 2.069, 2.175 Ultra Core 1.600, 1.651, 1.705 AL 110, 120 ZINC 44-24-18; 44-28-18 Premier 720, 725, 730, 735 Superior 810, 820 HELIX 3, 5, 7.5 P Series 160/2-30, 180/2-35, 180/4-35</p>
2.8" - 3"	<p>CD 10, 12, 14 CDN 10, 12, 14 LX 18, 20 ECO 6, 8, 10 HPSP 57, 60, 63 Rigid Curl 2.486 Ultra Core 1.792, 1.832, 2.000, 2.076 AL 140, 160, 180, 200 ZINC 51-32-18; 51-36-18 Premier 750, 755, 760 Superior 840, 850 HELIX 10, 15, 20 P Series 200/6-35, 212/6-40</p>	<p>CD 10, 12, 14 CDN 10, 12, 14 LX 18, 20 ECO 6, 8, 10 HPSP 51, 54, 57, 60 Rigid Curl 2.486 Ultra Core 1.792, 1.832, 2.000, 2.076 AL 140, 160, 180, 200 ZINC 51-32-18; 51-36-18 Premier 750, 755, 760 Superior 840, 850 HELIX 10, 15, 20 P Series 180/6-35, 200/6-35, 212/6-40</p>	<p>CD 10, 12, 14 CDN 10, 12, 14 LX 18, 20 ECO 6, 8, 10 HPSP 51, 54, 57, 60 Rigid Curl 2.486 Ultra Core 1.792, 1.832, 2.000, 2.076 AL 140, 160, 180, 200 ZINC 51-32-18; 51-36-18 Premier 750, 755, 760 Superior 840, 850 HELIX 10, 15, 20 P Series 200/6-30, 212/6-40, 214/4-40</p>	<p>CD 7, 8 CDN 7, 8 LX 14, 16 ECO 8, 10, 12 HPSP 48, 51, 54 Rigid Curl 2.175 Ultra Core 1.651, 1.705, 1.792, 1.832, 2.000 AL 140, 160, 180 ZINC 44-28-18; 51-32-18 Premier 735, 740, 745, 750 Superior 820, 830 HELIX 7.5, 10, 15 P Series 200/6-35, 212/6-40</p>	<p>CD 7, 8 CDN 7, 8 LX 14, 16 ECO 8, 10, 12 HPSP 39, 42, 45, 48, 51 Rigid Curl 2.175 Ultra Core 1.651, 1.705, 1.792, 1.832, 2.000 AL 140, 160, 180 ZINC 44-28-18; 51-32-18 Premier 735, 740, 745, 750 Superior 820, 830 HELIX 7.5, 10, 15 P Series 200/6-35, 212/6-40</p>

This chart is provided for informational purposes and is not meant to be used as a substitute for testing candles. Results from this chart are not guaranteed. Proper testing should be performed on each container/wick/wax/fragrance combination. NorthWood is not responsible for any products you make with our supplies, recipes or informational resources.

Wick Size Chart | 3-4" Containers

Version 5; Updated December 2023

DISTRIBUTING

Container Diameter	Ceda Serica	EC-26	CB-2	Soy	Coconut 83
3" - 3.5"	CD 10, 12, 14 CDN 10, 12, 14 LX 20, 21, 22 ECO 12, 14 HPSP 60, 63, 66 Rigid Curl 2.486, 2.552 Ultra Core 2.000, 2.076, 2.164, 2.283, 2.300 AL 180, 200, 210, 220 ZINC 60-44-18; 62-52-18 Premier 760, 765, 767, 770, 775, 777, 780, 785 Superior 850, 860 HELIX 20, 25, 30 P Series 214/4-40	CD 10, 12, 14 CDN 10, 12, 14 LX 20, 21, 22 ECO 12, 14 HPSP 54, 57, 60, 63 Rigid Curl 2.486, 2.552 Ultra Core 2.000, 2.076, 2.164, 2.283, 2.300 AL 180, 200, 210, 220 ZINC 60-44-18; 62-52-18 Premier 760, 765, 767, 770, 775, 777, 780, 785 Superior 850, 860 HELIX 20, 25, 30 P Series 214/4-40	CD 10, 12, 14 CDN 10, 12, 14 LX 20, 21, 22 ECO 12, 14 HPSP 54, 57, 60, 63 Rigid Curl 2.486, 2.552 Ultra Core 2.000, 2.076, 2.164, 2.283, 2.300 AL 180, 200, 210, 220 ZINC 60-44-18; 62-52-18 Premier 760, 765, 767, 770, 775, 777, 780, 785 Superior 850, 860 HELIX 20, 25, 30 P Series 212/6-40, 214/4-40	CD 8, 10, 12 CDN 8, 10, 12 LX 16, 18, 22 ECO 10, 12, 14 HPSP 54, 57, 60 Rigid Curl 2.175, 2.275 Ultra Core 1.792, 1.832, 2.000, 2.300, 2.402, 2.592 AL 140, 180, 200, 210 ZINC 51-32-18; 60-44-18 Premier 750, 755, 760, 765, 767 Superior 830, 840, 850 HELIX 15, 20, 25 P Series 212/6-40, 214/4-40	CD 8, 10, 12 CDN 8, 10, 12 LX 16, 18, 22 ECO 10, 12, 14 HPSP 48, 51, 54, 57 Rigid Curl 2.175, 2.275 Ultra Core 1.792, 1.832, 2.000, 2.300, 2.402, 2.592 AL 140, 180, 200, 210 ZINC 51-32-18; 60-44-18 Premier 750, 755, 760, 765, 767 Superior 830, 840, 850 HELIX 15, 20, 25 P Series 212/6-40, 214/4-40
3.5" - 4"	CD 16, 18, 20 CDN 16, 18, 20 LX 21, 22, 24, 26 ECO 14, 16 HPSP 63, 66 Ultra Core 2.164, 2.283, 2.300, 2.402, 2.592, 2.672, 2.775, 3.000 AL 220, 240 ZINC 62-52-18 Premier 780, 785, 790, 793, 795, 798, 799, 799-2, 799-4, 799-6, 799-8 Superior 860, 870 HELIX 30, 35, 40, 50 P Series 218/2-35	CD 16, 18, 20 CDN 16, 18, 20 LX 21, 22, 24, 26 ECO 14, 16 HPSP 60, 63, 66 Ultra Core 2.164, 2.283, 2.300, 2.402, 2.592, 2.672, 2.775, 3.000 AL 220, 240 ZINC 62-52-18 Premier 780, 785, 790, 793, 795, 798, 799, 799-2, 799-4, 799-6, 799-8 Superior 860, 870 HELIX 30, 35, 40, 50 P Series 218/2-35	CD 16, 18, 20 CDN 16, 18, 20 LX 21, 22, 24, 26 ECO 14, 16 HPSP 60, 63, 66 Ultra Core 2.164, 2.283, 2.300, 2.402, 2.592, 2.672, 2.775, 3.000 AL 220, 240 ZINC 62-52-18 Premier 780, 785, 790, 793, 795, 798, 799, 799-2, 799-4, 799-6, 799-8 Superior 860, 870 HELIX 30, 35, 40, 50 P Series 218/2-35	CD 12, 14, 16 CDN 12, 14, 16 LX 18, 20, 21, 22, 24 ECO 14, 16 HPSP 60, 63, 66 Ultra Core 2.000, 2.076, 2.164, 2.283, 2.300, 2.402, 2.592 AL 210, 220, 240 ZINC 60-44-18 Premier 765, 767, 770, 775, 777, 780, 785 Superior 850, 860 HELIX 25, 30, 35, 40 P Series 214/4-40, 218/2-35	CD 12, 14, 16 CDN 12, 14, 16 LX 18, 20, 21, 22, 24 ECO 14, 16 HPSP 57, 60, 63, 66 Ultra Core 2.000, 2.076, 2.164, 2.283, 2.300, 2.402, 2.592 AL 210, 220, 240 ZINC 60-44-18 Premier 765, 767, 770, 775, 777, 780, 785 Superior 850, 860 HELIX 25, 30, 35, 40 P Series 214/4-40, 218/2-35

How to Make Multi-Wick Candles

Candles made in large containers – such as 3.5" in diameter or more – can be more difficult to wick. For large candles, you might find it works better to double-wick or triple-wick your candle.

Double-wicking a candle is when you use two wicks instead of one. The wicks should be evenly spaced from one another and from the walls of the container.

To choose a wick size, divide the diameter of the container in half. Then use the wick chart to choose a wick size that is appropriate for half the diameter of the jar. For example, a 4" diameter soy wax candle may be suitable wicked with two LX 10 wicks rather than one LX 24 wick.

To make a triple-wick candle, divide the diameter of the container by 3. Use the chart to choose a wick that is appropriate for the new diameter (1/3 of the jar). Just like double-wicked candles, space the wicks an equal distance apart from each other and from the walls of the container.