CLASSIC 85 PUMP SERIES SPECIFICATIONS STENNER PUMPS

SINGLE HEAD ADJUSTABLE OUTPUT





100 psi (6.9 bar) MODELS

- · 85MHP5
- · 85MHP17
- · 85MHP40

25 psi (1.7 bar) MODELS

- · 85M1
- ·85M2
- · 85M3
- · 85M4
- · 85M5





SHIPPING WEIGHT 9 lbs (4 kg)

SINGLE HEAD FIXED OUTPUT





100 psi (6.9 bar) MODELS

- · 85MPHP5
- · 85MPHP17
- · 85MPHP40

25 psi (1.7 bar) MODELS

- ·85MP1
- · 85MP2
- · 85MP3
- · 85MP4
- · 85MP5





SHIPPING WEIGHT 8 lbs (3.6 kg)

METERING PUMP











Product listings vary by model. Contact factory for details.

FEATURES

- · 3-point roller design assists in anti-siphon protection
- Pump head requires no valves, allows for easy maintenance
- Self-priming against maximum working pressure, foot valve not required
- Pump does not lose prime or vapor lock
- Pumps off-gassing solutions and can run dry
- · Output volume is not affected by back pressure
- Injection check valve included with models rated up to 100 psi (6.9 bar)
- · Easy to change pump tube; lubrication is not required
- · Pump tubes and pump heads interchange between models
- · Models tested by Water Quality Association to conform to ANSI/NSF STD 61 (Santoprene® only)
- · Adjustable models tested by ETL to conform to ANSI/NSF STD 50
- · All pump accessories included allow a fast and easy installation



CLASSIC 85 PUMP SERIES SPECIFICATIONS STENNER PUMPS

OUTPUT CONTROL

Adjustable models only, external dial ring adjustment from 5%-100% in 2.5% increments

MAXIMUM WORKING PRESSURE

100 psi (6.9 bar) 85MHP5, 85MHP17, 85MHP40, 85MPHP5, 85MPHP17, 85MPHP40 25 psi (1.7 bar) 85M1, 85M2, 85M3, 85M4, 85M5, 85MP1, 85MP2, 85MP3, 85MP4, 85MP5

MAXIMUM OPERATING TEMPERATURE 125° F (52° C)

MAXIMUM SUCTION LIFT

25 ft (7.6 m) vertical lift, based on water

MOTOR TYPE

1/30 HP, shaded pole, class B

APPROXIMATE GEAR MOTOR RPM

DUTY CYCLE Continuous

MOTOR VOLTAGE (AMP DRAW)

120V 60Hz 1PH (1.7) 220V 60Hz 1PH (0.9)

230V 50Hz 1PH (0.9) International

250V 50Hz 1PH (0.9) International

POWER CORD TYPE

SJTOW

85M5

POWER CORD PLUG END

120V 60Hz NEMA 5/15 220V 60Hz NEMA 6/15 230V 50Hz CEE 7/VII 250V 50Hz CEE 7/VII

MATERIALS OF CONSTRUCTION

Peristaltic tube Santoprene®*and optional Tygothane®**, FDA approved

Tube fittings, compression nuts Type 1 rigid PVC. NSF listed

Suction strainer & weight PP or Type 1 rigid PVC body with Type 1 rigid PVC cap, ceramic weight, NSF listed

Suction/discharge tubing & ferrules LDPE polyethylene, NSF and FDA approved

Check valve (injection fitting & body)

Type 1 rigid PVC, NSF listed

Check valve duckbill

Santoprene®*, FDA approved Pellathane®† (with Tygothane®** tube)

All pump housings Polycarbonate plastic

Pump head rollers HDPE

Roller bushings Oil impregnated sintered bronze

All fasteners Stainless steel

ACCESSORY KIT SHIPPED WITH EACH PUMP

- 3 connecting nuts 1/4" or 3/8"
- 3 ferrules 1/4" or 6 mm Europe OR 2 ferrules 3/8"
- 1 injection check valve 100 psi (6.9 bar) OR 1 injection fitting 25 psi (1.7 bar)
- 1 weighted suction line strainer 1/4", 3/8" or 6 mm Europe
- 1 20' roll suction/discharge tubing 1/4" or 3/8" white or UV black OR 6 mm white Europe
- 1 spare pump tube
- 1 mounting bracket
- 1 manual

- Santoprene® is a registered trademark of Exxon Mobil Corporation.
- ** Tygothane* is a registered trademark of Saint-Gobain Performance Plastics.
- † Pellathane* is a registered trademark of The Dow Company.

Approximate Outputs @ 50Hz

85 SERIES PUMP ADJUSTABLE OUTPUT

Single Head Model	Maximum Pressure	Pump Tube Number	Gallons per Day	Liters per Day	Gallons per Hour	Liters per Hour	Ounces per Minute	Milliliters per Minute	Liters per Day	Liters per Hour	Milliliters per Minute
85MHP5° 85M1	100 psi (6.9 bar) 25 psi (1.7 bar)	#1 #1	0.3 to 5.0	1.1 to 18.9	0.01 to 0.21	0.05 to 0.79	0.03 to 0.44	0.76 to 13.13	0.9 to 15.1	0.04 to 0.63	0.52 to 10.49
85MHP17° 85M2	100 psi (6.9 bar) 25 psi (1.7 bar)	#2 #2	0.8 to 17.0	3.0 to 64.4	0.03 to 0.71	0.13 to 2.68	0.07 to 1.51	2.08 to 44.65	2.4 to 51.5	0.10 to 2.15	1.67 to 35.76
85MHP40° 85M3	100 psi (6.9 bar) 25 psi (1.7 bar)	#7 #3	2.0 to 40.0	7.6 to 151.4	0.08 to 1.67	0.32 to 6.31	0.18 to 3.55	5.27 to 105.14	6.1 to 121.1	0.25 to 5.05	4.24 to 84.10
85M4	25 psi (1.7 bar)	#4	3.0 to 60.0	11.4 to 227.1	0.13 to 2.50	0.48 to 9.46	0.27 to 5.33	7.92 to 157.71	9.1 to 181.7	0.38 to 7.57	6.32 to 126.18

4.3 to 85.0 16.3 to 321.8 0.18 to 3.54 0.68 to 13.40 0.38 to 7.55 11.32 to 223.40 3.0 to 257.4 0.54 to 10.73 9.03 to 178.75

Approximate Outputs @ 60Hz ___

85 SERIES PUMP FIXED OUTPUT

25 psi (1.7 bar)

			Approximate outputs @ 60Hz							Approximate Outputs @ 50Hz —		
Single Head Model	Maximum Pressure	Pump Tube Number	Gallons per Day	Liters per Day	Gallons per Hour	Liters per Hour	Ounces per Minute	Milliliters per Minute	Liters per Day	Liters per Hour	Milliliters per Minute	
85MPHP5° 85MP1	100 psi (6.9 bar) 25 psi (1.7 bar)	#1 #1	5.0	18.9	0.21	0.79	0.44	13.13	15.1	0.63	10.49	
85MPHP17 ⁻ 85MP2	100 psi (6.9 bar) 25 psi (1.7 bar)	#2 #2	17.0	64.4	0.71	2.68	1.51	44.65	51.5	2.15	35.76	
85MPHP40 ⁻ 85MP3	100 psi (6.9 bar) 25 psi (1.7 bar)	#7 #3	40.0	151.4	1.67	6.31	3.55	105.14	121.1	5.05	84.10	
85MP4	25 psi (1.7 bar)	#4	60.0	227.1	2.50	9.46	5.33	157.71	181.7	7.57	126.18	
85MP5	25 psi (1.7 bar)	#5	85.0	321.8	3.54	13.40	7.55	223.40	257.4	10.73	178.75	

*Injection check valve included with pumps rated 26-100 psi (1.8-6.9 bar).



NOTICE: The information within this chart is solely intended for use as a guide. The output data is an approximation based on pumping water under a controlled testing environment. Many variables can affect the output of the pump. Stenner Pump Company recommends that all metering pumps undergo field calibration by means of analytical testing to confirm their outputs. The information contained in this flyer is not intended for specific application purposes. Stenner Pump Company reserves the right to make changes to prices, products, and specifications at any time without prior notice.