

Fluorescent Penetrant Equipment



Equipcon's Value Line FPI Equipment is offered in 8 different models.

Each model has different options for method, stations, and lengths.



Model	Method	Stations	Length
PT-C	General	Stand alone penetrant station, includes: solid table-top, back and roof, side and front curtains, overhead UV lamp, white light, and ventilation fan	4'
WW-73	Method A (Water Washable)	PT/Dwell/Rinse/Dry/Rest/Develop/Inspect 12" x 18" Tanks	9'
H-73	Method D (PE Hydrophilic)	PT/Dwell/Emulsifier/Rinse/Dry/Rest/Develop/Inspect 12" x 18" Tanks	10'
WW-82	Method A (Water Washable)	PT/Dwell/Pre-Rinse/Emulsifier/Post-Rinse/Dry/Rest/Develop/Inspect 18" x 24" Tanks	15'
H-82	Method D (PE Hyrdophilic)	PT/Dwell/Emulsifier/Rinse/Dry/Rest/Develop/Inspect 18" x 24" tanks	18'
FPI-Inspect	Station	Stand alone inspection station with UV White Light	3' x 3' x 7'
FPI-G100WW	Method A (Water Washable)	Fully Automatic 108"L x 48"W x 8"H Baskets Footprint 8"L x 18"W x 6"H	9'
FPI-G100H	Method D (PE Hydrophilic)	Fully Automatic 108"L x 48"W x 8"H Baskets Footprint 8"L x 18"W x 6"H	13'