



C-MAG MS 4 IKAMAG®

New magnetic stirrer without heating. With ceramic set-up plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 5 I (H2O)
- Elevated control panel for protection against leaking liquids

Accessories: RS 1 Set of magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated

Technical Data	
Number of stirring positions	1
Stirring quantity max. (H2O) [I]	5
Motor rating input [W]	15
Motor rating output [W]	1.5
Speed display	scale
Speed range [rpm]	100 - 1500
Speed control	scale 0 - 6
Set-up plate material	ceramic
Set-up plate dimensions [mm]	100 x 100
Dimensions (W x H x D) [mm]	150 x 105 x 260
Weight [kg]	3
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230 / 120 / 100
Frequency [Hz]	50/60
Power input [W]	30
Ident. No.	0003582201

Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, RSE Stirring bar remover, H 16 V Support rod, LABLIFT m