



Prolab[®] Asset Labels

The Prolab[®] Asset labels are made from a durable polyester with a strong adhesive to ensure long-term bonding.

Typically, they can be used to label both assets and equipment. These labels are designed for internal use.

Print in conjunction with our DTP-1/300 Plug'N'Play thermal printer with the same ribbon as all our other thermal labels.

A 300m thermal ribbon will yield approximately 50,000 60mm x 10mm labels.

TECHNICAL DATA

Printing method:	DTP-1 Printer
Thermal Ribbon:	TSR3
Material:	Self-adhesive Polyester
Thickness:	56 micron
RoHS:	Yes
Reach:	Yes

Test	Method
Elevated Temperature**	MIL-STD-202G Method 108A - 2000 hrs @ 70°C to 100°C
Low Temperature*	MIL-STD-810 Method 502.4 - 72 hrs @ 40°C
H2S Sour Gas	Exposure (2% H2S)
Salt Mist Spray	EC60068-2-52 Test kb Salt Mist (Cyclic)
UV Weathering	ISO 4982 Part 4 Method A Cycle 1 - 2000hrs Silver - 3000 hrs White

*Manipulation of the labels were performed at -40°C at completion of the low temperature test.

**Samples were subjected to 500 hours @ 70°C followed by 500 hours @ 85°C followed by 1000 hours @100°C



For more information and to discuss your needs please contact our sales team on: +44 (0)1707 37 37 27 or email sales@silverfox.co.uk | www.silverfox.co.uk | support@silverfox.co.uk

Prolab[®], Labacus Innovator[®] and Fox-in-a-Box[®] are registered Trademarks of Silver Fox Group Limited, Licensed to Silver Fox Limited -© Silver Fox Limited, 2023

Copyright © Silver Fox | 2023 Version 2





Prolab[®] Asset Labels

Additional Information

Use with Silver Fox Labacus Innovator[®] Advanced or Professional software.
 Print in conjunction with our Fox-in-a-Box[®] Plug'N'Play thermal printer using the same ribbon as all our other thermal labels.

ORDER INFORMATION

Product Code	Label Dimensions (mm)	Labels per Roll	Pack Qty	Labels per Pack	Colour
P/AT01/5025T	50 x 25	2500	1 Roll	2500	○ ●
P/AT01/6010T	60 x 10	5000	1 Roll	5000	○ ●



STORAGE INSTRUCTIONS

Storage Instructions	Store between 50°F (10°C) and 77°F (25°C)
Conditions	Keep in dark conditions
Humidity Resistance	35% to 65% RH

Disclaimer: The information contained in this datasheet is based on data we believe to be reliable and is given for information only and without guarantee and does not constitute a warranty. We are not able to anticipate every set of conditions, so always suggest that users should also satisfy themselves as to the suitability of our products for their particular environment and application and not make any assumptions based on information in this data sheet that is included or omitted. This datasheet supersedes any previous information/datasheet released and is subject to change without notice.E&OE.

For more information and to discuss your needs please contact our sales team on: +44 (0)1707 37 37 27 or email sales@silverfox.co.uk | www.silverfox.co.uk | support@silverfox.co.uk

Prolab[®], Labacus Innovator[®] and Fox-in-a-Box[®] are registered Trademarks of Silver Fox Group Limited, Licensed to Silver Fox Limited -© Silver Fox Limited, 2023

Copyright © Silver Fox | 2023 Version 2

