

## Separations | GC column SolGel-WAX™

Part number	Part description and detail
0547100	0.1 mm ID x 0.1 µm film thickness x 10 m length SolGel-WAX GC capillary column
054796	0.25 mm ID x 0.25 µm film thickness x 30 m length SolGel-WAX GC capillary column
054791	0.25 mm ID x 0.25 µm film thickness x 60 m length SolGel-WAX GC capillary column
054787	0.25 mm ID x 1.0 µm film thickness x 30 m length SolGel-WAX GC capillary column
054788	0.32 mm ID x 0.25 µm film thickness x 30 m length SolGel-WAX GC capillary column
054789	0.32 mm ID x 0.25 µm film thickness x 60 m length SolGel-WAX GC capillary column
054797	0.32 mm ID x 0.5 µm film thickness x 30 m length SolGel-WAX GC capillary column
054792	0.32 mm ID x 0.5 µm film thickness x 60 m length SolGel-WAX GC capillary column
0547851	0.53 mm ID x 0.1 µm film thickness x 30 m length SolGel-WAX GC capillary column
054786	0.53 mm ID x 0.5 µm film thickness x 30 m length SolGel-WAX GC capillary column
054785	0.53 mm ID x 1.0 µm film thickness x 30 m length SolGel-WAX GC capillary column

For more information about this product visit [www.trajanscimed.com](http://www.trajanscimed.com) or contact [techsupport@trajanscimed.com](mailto:techsupport@trajanscimed.com)