




<b>Product</b> <b>Item number</b>	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout R8652000
<b>Colour</b>  <b>Product description</b>	<p>VVS: 777637220          NRF: 7501969          EAN: 5708590338316          HMI: 48880</p> <p>White</p>  <p>Pressalit offers a wide range of daycare changing tables, both free-standing and wall-hung, in several sizes and models. The wall-hung tables are also available in versions where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves.</p> <p>All types of daycare changing tables are available in versions with sanitary appliances and a choice of taps, with or without pull-out shower heads.</p> <p>Freestanding changing table with sanitary appliances, 800 x 1400 mm. With electric motor and transformer, height adjustable from 650 mm - 1000 mm, with wired hand control.</p> <p>Molded worktop with integrated sink, incl. lever operated mixer tap, pull-out shower head, feed/waste system and 2 wire baskets.</p> <p>Materials: ABS plastics, synthetic acrylic and powder-lacquered steel.</p>
<b>Adjustability</b> <b>Adjustment height</b>  <b>Product capacity</b> <b>Speed upwards</b>  <b>Noise level</b>	<p>Height adjustable</p> <p>350 mm</p> <p>Max load: 75 kg.</p> <p>Speed up mm: 14 mm/s          Speed down mm: 14 mm/s</p> <p>48 dB</p>
<b>Materials</b>	<p>Lifting unit and baskets: Powder-laquered steel.          Worktop: ABS with acrylic.          Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.</p>



<b>Product</b>	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
<b>Item number</b>	R8652000
<b>Ergonomy</b>	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.
<b>Features</b>	Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap with pull-out spout.
<b>Mains connection (V)</b>	230
<b>Actuator (motor)</b>	LA31 Deskline (Linak), 1500N, IPX1
<b>Control box</b>	CBD6 (Linak), IP20
<b>Wired remote control</b>	HB30 (Linak), IPX4
<b>Power consumption (maximum load)</b>	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
<b>Cleaning</b>	<p>Changing table. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>



PRESSALIT®

<b>Product</b>	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
<b>Item number</b>	R8652000
<b>Declaration of conformity</b>	<p>CE UK MASK-ROHS This product complies with the relevant requirements of:</p> <ul style="list-style-type: none"><li>- Council Directive 2006/42/EC on machinery</li><li>- Council Directive 2011/65/EC on RoHS.</li></ul> <p><b>For the UK:</b> - The Supply of Machinery (Safety) Regulations 2008</p> <ul style="list-style-type: none"><li>- Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012</li></ul>

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®