

FILTRATION | SEPARATION | PURIFICATION

COAX[™] Series Filter Cartridges

Two Stage Depth Filter Cartridge

The COAX Depth Filter cartridge is an integral two stage depth filter. The first stage is made of nonwoven melt blown polypropylene to trap coarser particles. The second stage is composed of a bicomponent polypropylene and polyethylene fiber to provide fine particle retention. This unique design provides a true graded, two zone structure that offers a marked increase in useful life and dirt capacity. In addition, the rigid nature means there is no flexing of the cartridge and greatly reducing media migration and particle unloading.

Features-Benefits

- Two stage depth filter
- · Maximum dirt holding and useful life
- Inert pure polyolefin construction, non-shedding media
- Broad chemical compatibility
- Low extractables
- Extensive range of lengths and configurations
- Rigid construction resists unloading

Product Specifications

Media:	Thermally bonded Polypropylene/polyethylene fiber		
End caps:	Polypropylene (when used)		
Gaskets/O-Rings :	Silicone, EPDM, Buna N, Santoprene, Viton, PTFE encapsulated Viton (O-Rings only)		
Micron ratings:	0.5, 1, 3, 5, 10, 25 μm		
Dimensions			
•	", 9.75", 10", 20", 30", 40" 2.7, 24.8, 25.4, 50.8, 76.2, 101.6 cm)		
Outside diameter:	2.6" (6.5 cm)		
Inside diameter:	1.0" (2.54 cm)		
Operating Parameter	ers		
Maximum operating	140 °F (60°C)		
Maximum differential pressure:	100 psid @ 70°F (7 bar @ 21°C) 2 psid @ 176°F (0.14 bar @ 80°C)		
Recommended change-out pressure:	35 psid (2.4 bar)		

Performance Specifications

Sanitization

Hot water at $176^{\circ}F$ ($80^{\circ}C$) at 2 psid (0.14 bar) for 30 min. In-line steam at $257^{\circ}F$ ($125^{\circ}C$) at 1 psid (0.07 bar) for 30 min. Autoclavable at $257^{\circ}F$ ($125^{\circ}C$) for 30 min.



Certifications

USP Class VI - Meets USP Class VI Biological Test for Plastics


FDA Listed Materials - All Materials comply with FDA Title 21 of the Code of Federal Regulations Sections 174.5, and 177.1520, as applicable for food and beverage contact.

Typical Applications

- Paint
- Perfumes
- Cutting Oils
- CMP Slurries
- Magnetic Slurries
- Corn Syrup
- Plating Solutions
- Pre R.O.
- Coatings

COAX Nomenclature Information RL **COAX** 25 -40 **P3** В **COAX** Series Filters **End Configuration Gasket or O-Ring** Double Open End Silicone Ρ S **Retention Rating** В Buna-N **P2** 226/Flat Single Open End (microns) **EPDM** Ε Р3 222/Flat Single Open End 0.5 3 10 ٧ Viton **P6** Self-Seal Spring on One End 5 25 Т Teflon endcap. **P7** 226/Fin Single Open End Viton (O-Rings only) **P8** 222/Fin Single Open End **Nominal Length (inches)** N None PX Extended Core -30 Ν None (Cut Ends) -9.75 -20 -40 Single Open End, internal O-Ring AM **DBG** Direct Bond Santoprene Gaskets **Length Option** Blank Standard length Reduced length

Example: COAX 25-40RLP3B



Removal Efficiency

Beta Ratio Efficiency	Beta 10 90%	Beta 20 95%	Beta 100 99%
0.5 micron	0.5	2.0	4.0
1 micron	1.0	3.0	8.0
3 microns	3.0	5.0	12.0
5 microns	5.0	8.0	20.0
10 microns	10.0	13.0	30.0
25 microns	25.0	30.0	50.0

COAX is a trademark of Graver Technologies, LLC.



75 Elmview Ave. Hamburg, NY 14075 Phone: 716.649.2326 Fax: 716.649.9006

www.filtersource.com