



Adapter Configuration 1

EZwaste® Filter Kit, VersaCap® Cap, 6 ports for 1/8" OD Tubing




SKU	CONTAINER SIZE	1/4" OD PORTS	1/8" OD PORTS	1/16" OD PORTS	1/4" or 3/8" HB PORT	FLUID LEVEL SENSOR PORT
UN/DOT APPROVED CONTAINERS						
330-0B03-OEM	CAP ONLY		6			
332-AB03-OEM	13.5L		6			
332-BB03-OEM	20L		6			
HEAVY DUTY REUSABLE CONTAINERS						
330-0412-OEM	CAP ONLY		6			
332-9412-OEM	4L		6			
332-2412-OEM	5L		6			
332-3412-OEM	10L		6			
332-4412-OEM	20L		6			
332-D412-OEM	20L ROUND		6			



Adapter Configuration 2


EZwaste® Filter Kit, VersaCap® Cap, 6 ports for 1/16" OD Tubing



SKU	CONTAINER SIZE	1/4" OD PORTS	1/8" OD PORTS	1/16" OD PORTS	1/4" or 3/8" HB PORT	FLUID LEVEL SENSOR PORT
UN/DOT APPROVED CONTAINERS						
330-0B01-OEM	CAP ONLY			6		
332-AB01-OEM	13.5L			6		
332-BB01-OEM	20L			6		

Adapter Configuration 3

EZwaste® Filter Kit, VersaCap® Cap, 6 ports for 1/8" OD Tubing, 1 port for 1/4" HB or 3/8" HB




SKU	CONTAINER SIZE	1/4" OD PORTS	1/8" OD PORTS	1/16" OD PORTS	1/4" or 3/8" HB PORT	FLUID LEVEL SENSOR PORT
UN/DOT APPROVED CONTAINERS						
330-0B05-OEM	CAP ONLY		6		1	
332-AB05-OEM	13.5L		6		1	
332-BB05-OEM	20L		6		1	
HEAVY DUTY REUSABLE CONTAINERS						
330-0418-OEM	CAP ONLY		6		1	
332-9418-OEM	4L		6		1	
332-2418-OEM	5L		6		1	
332-3418-OEM	10L		6		1	
332-4418-OEM	20L		6		1	
332-D418-OEM	20L ROUND		6		1	




Solvent Waste System Sizing Guide

- For measuring OD, place the tube next to each of the images to determine the correct size of the tubing.




- For measuring ID, place end of tube flat on the piece of paper and determine if the dark area is contained by the tubing.




Adapter Configuration 4

EZwaste® Filter Kit, VersaCap® Cap, 4 ports for 1/8" OD Tubing, 3 ports for 1/4" OD Tubing




SKU	CONTAINER SIZE	1/4" OD PORTS	1/8" OD PORTS	1/16" OD PORTS	1/4" or 3/8" HB PORT	FLUID LEVEL SENSOR PORT
UN/DOT APPROVED CONTAINERS						
330-0B11-OEM	CAP ONLY	3	4			
332-AB11-OEM	13.5L	3	4			
332-BB11-OEM	20L	3	4			
HEAVY DUTY REUSABLE CONTAINERS						
330-0413-OEM	CAP ONLY	3	4			
332-9413-OEM	4L	3	4			
332-2413-OEM	5L	3	4			
332-3413-OEM	10L	3	4			
332-4413-OEM	20L	3	4			
332-D413-OEM	20L ROUND	3	4			



Adapter Configuration 5

EZwaste® Filter Kit, VersaCap® Cap, 4 ports for 1/8" OD Tubing, 4 ports for 1/4" OD Tubing



SKU	CONTAINER SIZE	1/4" OD PORTS	1/8" OD PORTS	1/16" OD PORTS	1/4" or 3/8" HB PORT	FLUID LEVEL SENSOR PORT
UN/DOT APPROVED CONTAINERS						
330-0B16-OEM	CAP ONLY	4	4			
332-AB16-OEM	13.5L	4	4			
332-BB16-OEM	20L	4	4			
HEAVY DUTY REUSABLE CONTAINERS						
330-0421-OEM	CAP ONLY	4	4			
332-9421-OEM	4L	4	4			
332-2421-OEM	5L	4	4			
332-3421-OEM	10L	4	4			
332-4421-OEM	20L	4	4			
332-D421-OEM	20L ROUND	4	4			

Adapter Configuration 6

EZwaste® Filter Kit, VersaCap® Cap, 4 ports for 1/8" OD Tubing, 3 ports for 1/4" OD Tubing, 1 port for 1/4" HB or 3/8" HB



SKU	CONTAINER SIZE	1/4" OD PORTS	1/8" OD PORTS	1/16" OD PORTS	1/4" or 3/8" HB PORT	FLUID LEVEL SENSOR PORT
UN/DOT APPROVED CONTAINERS						
330-0B15-OEM	CAP ONLY	3	4		1	
332-AB15-OEM	13.5L	3	4		1	
332-BB15-OEM	20L	3	4		1	
HEAVY DUTY REUSABLE CONTAINERS						
330-0419-OEM	CAP ONLY	3	4		1	
332-9419-OEM	4L	3	4		1	
332-2419-OEM	5L	3	4		1	
332-3419-OEM	10L	3	4		1	
332-4419-OEM	20L	3	4		1	
332-D419-OEM	20L ROUND	3	4		1	



Note: All variations of the EZwaste® Filter Kit come with plugs for all VersaCap® ports. Unused ports can be plugged to ensure proper functionality of the system.