

Power Portfolio







The Quickie QM-7 series offers a high-performing, reliable, and stylish mid-wheel drive power solution for a client who qualifies for a Group 3 Standard (QM-710), Group 3 Heavy Duty (QM-715 HD) or Group 4 High Speed (QM-720) power mobility base.

QUICKIE OM-7 Series



Available in Eight Group 3 and Group 4 Models:

GROUP 3: Standard Wt. Cap.

- Quickie QM-710 BC (K0848): No Power Option Base with ASAP II Rehab Seat
- Quickie QM-710 SC (K0856): Single Power Option Tilt (SPOT) or Recline Base with ASAP II or Recline Rehab Seat
- Quickie QM-710 MPC (K0861): Multiple Power Option Base (SPOT Tilt and Recline) with 3.7 Recline Seat

GROUP 3: Heavy Duty

- Quickie QM-715 HD BC (K0850): No Power Option Base with ASAP II Rehab Seat
- Quickie QM-715 HD SC (K0858): Single Power Option Tilt (SPOT) with ASAP II Rehab Seat
- Quickie QM-715 HD MPC (K0862): Multiple Power Option Base (SPOT Tilt and Recline) with 3.7 Recline Seat

GROUP 4: High Activity

- Quickie QM-720 BD (K0868): No Power Option Base with ASAP II Rehab Seat
- Quickie QM-720 SD (K0877): Single Power Option Tilt (SPOT) or Recline Base with ASAP II or Recline Rehab Seat
- Quickie QM-720 MPD (K0884): Multiple Power Option Base (SPOT Tilt and Recline) with 3.7 Recline Seat



Power Base Performance

- · Linix 5 mph, 6 mph, or 8 mph, 4-pole motor packages
- Intuitive mid-wheel drive handling
- Contoured, sleek base available in 15 shroud color options
- SpiderTrac[™] Suspension for superior traction and handling across multiple terrains
 - Gas dampening system for smooth transitions
 - 3" curb climbing capability
 - 22° transition angle helps prevent high centering on curb cuts



Seating Options

ASAP II Seat Frame

- · In-field width, depth, armrest, legrest, and back height adjustability
- Wide range of seat sizes
- · Manual reclining backrest for increased function and sitting tolerance
- · Optional fold down backrest for easy transport
- · Extensive seating and positioning options

3.7 Recline Seat Frame

- 14" 22" seat widths and depths
- Ultra low seat-to-floor heights as low as 16" when combined with tilt and elevate!
- Integrated JAY J3 back for seamless functionality with power recline and shear reduction system
- · Cantilever Reclining Armrests for optimal positioning at any back angle
- Low profile electronics enclosure shell for a clean look and compatibility with accessories



Power Options

- NEW 3.7 Power Recline with Power Shear Reduction
- 50° of Power Tilt to optimize positioning
- 12" and 9" Power Seat Elevate for increased access to cabinets and interaction with peers
- Power Elevating Legrests with Articulation
 - Swing-Away
 - Centermount with Single/Dual Footplate for angle adjustability as a single footplate or separate footplates

Quickie QM-7 Series Specifications

SPECIFICATIONS	QM-710 BC	QM-710 SC	QM-710 MPC	QM-715 HD BC	QM-715 HD SC	QM-715 HD MPC	QM-720 BD	QM-720 SD	QM-720 MPD
HCPCS Code	K0848	K0856	K0861	K0850	K0858	K0862	K0868	K0877	K0884
Drive Wheel Position	Mid	Mid	Mid	Mid	Mid	Mid	Mid	Mid	Mid
Speed	6.0 mph*	6.0 mph*	6.0 mph*	5.0 mph	5.0 mph	5.0 mph	8.0 mph	8.0 mph	8.0 mph
Overall Weight	310 lbs.	350 lbs.	375 lbs.	310 lbs.	350 lbs.	375 lbs.	310 lbs.	350 lbs.	375 lbs.
Overall Width	25"	25"	25"	25"	25"	25"	25"	25"	25"
Overall Length	36" w/o footrests	36" w/o footrests	36" w/o footrests	36" w/o footrests	36" w/o footrests	36" w/o footrests	36" w/o footrests	36" w/o footrests	36" w/o footrests
User Weight Capacity	300 lbs.	300 lbs.	300 lbs.	400 lbs.	400 lbs.	350 lbs.	300 lbs.	300 lbs.	300 lbs.
Seat Widths	12" to 22"	12" to 22"	14" to 22"	16" to 22"	16" to 22"	16" to 22"	12" to 22"	12" to 22"	14" to 22"
Seat Depths	12" to 22"	12" to 22"	16" to 22"	16" to 22"	16" to 22"	16" to 22"	12" to 22"	12" to 22"	16" to 22"
Front Seat To Floor Height	17.5" to 20.5"	18" to 21"	16.5" to 19.5"	17.5" to 20.5"	18" to 21"	16.6" to 19.6"	17.5" to 20.5"	18" to 21"	16.5" to 19.5"
Seat Frame Options	ASAP II	ASAP II or 3.7 Recline	3.7 Recline	ASAP II	ASAP II	3.7 Recline	ASAP II or 3.7 Recline	ASAP II or 3.7 Recline	3.7 Recline
Power Seating Options	N/A	Tilt or Recline	Tilt & Recline	No Power Options	Tilt or Recline	Tilt & Recline	No Power Options	Tilt or Recline	Tilt & Recline

The Quickie Pulse is a compact, durable power wheelchair that offers a wide range of effective seating and electronics options to meet the needs of Group 3 users.

QUICKIE® Pulse™



Available in Five Models:

- Quickie Pulse 5 BC (K0848): 5 MPH, 2-pole motor, No Power Option base with ASAP II Rehab Seat
- Quickie Pulse 6 BC (K0848): 6 MPH, 4-pole motor, No Power Option base with ASAP II Rehab Seat
- Quickie Pulse 5 CC (K0849): 5 MPH, 2-pole motor, No Power Option base with Captain's Seat
- Quickie Pulse 6 CC (K0849): 6 MPH, 4-pole motor, No Power Option base with Captain's Seat
- Quickie Pulse 6 SC (K0856): 6 MPH, 4-pole motor, Single Power Option Tilt (SPOT) with ASAP II Rehab Seat



Compact Power Base

- · Intuitive mid-wheel drive handling
- · Small footprint and compact design for indoor accessibility
- Flexible, independent suspension system for moderate outdoor performance
 - Anti-pitching mechanism for smooth transitions
 - Linked suspension helps prevent high centering
- · Linix 2- or 4-pole motors



Seating Options

Captain's Seat (CC)

- · Comfortable style
- Convertible seat pan for flexibility in seating options
- · Semi-recline and fold-down backrest
- · Seat size, legrest, and armrest adjustability
- · Mounting capabilities for O2, crutch, or walker holders
- · Low seat heights for increased accessibility

ASAP II

- In-field width, depth, armrest, legrest, and back height adjustability
- Wide range of seat sizes
- Manual reclining backrest for increased function and sitting tolerance
- Optional fold down backrest for easy transport
- Extensive seating and positioning options



Power Options

- 50° of Single Power Option Tilt (SPOT) to optimize positioning
- 9" Seat Elevate for increased access to cabinets and interaction with peers
- · Power Elevating Legrests with Articulation
 - Swing-away
 - Centermount

Quickie Pulse Specifications

SPECIFICATIONS	PULSE 5 BC	PULSE 6 BC	PULSE 5 CC	PULSE 6 CC	PULSE 6 SC
Drive Wheel Position	Mid	Mid	Mid	Mid	Mid
HCPCS Code	K0848	K0848	K0849	K0849	K0856
Speed	5.0 MPH	6.0 MPH	5.0 MPH	6.0 MPH	6.0 MPH
Overall Weight	235 lbs.	235 lbs.	250 lbs.	250 lbs.	260 lbs.
Overall Width	24"	24"	24"	24"	24"
Overall Length	34"	34"	34"	34"	34"
User Weight Capacity	300 lbs.	300 lbs.	300 lbs.	300 lbs.	300 lbs.
Seat Widths	12" to 22"	12" to 22"	16", 18", 20"	16", 18", 20"	12" to 22"
Seat Depths	12" to 22"	12" to 22"	14" to 22"	14" to 22"	12" to 22"
Front Seat To Floor Height	16.5" to 19.5"	16.5" to 19.5"	17" to 19"	17" to 19"	17.5" to 21.5"
Seating Frame Options	ASAP II Rehab Seat	ASAP II Rehab Seat	Captain's Seat	Captain's Seat	ASAP II Rehab Seat
Power Seating Options	No Power Options	No Power Options	No Power Options	No Power Options	Tilt

The Quickie S-636 features innovative, Group 3 performance and versatile seating and positioning options to accommodate both general and specialized rehabilitation needs.

QUICKIE'S-6 Series



Available in Six Group 3 and 4 Models:

- Quickie S-636 BC (K0848): No Power Option S-636 base with Rehab seat
- Quickie S-636 SC (K0856): Single Power Option (tilt or recline) S-636 base with Rehab or Recline seat
- Quickie S-636 MPC (K0861): Multi Power Option (tilt and recline) S-636 base with Rehab Recline seat
- Quickie S-646 SE BD (K0868): No Power Option S-646 SE base with Rehab seat
- Quickie S-646 SE SD (K0877): Single Power Option (tilt or recline) S-646 SE base with Rehab or Recline seat
- Quickie S-646 SE MPD (K0884): Multi Power Option (tilt and recline) S-646 SE base with Rehab Recline seat



Hybrid Base with Dynamic Suspension

- Linix 6.5 mph or 8.5 mph, 4-pole standard motor package for all models
- Short wheel base with hybrid wheel placement for mid-wheel maneuverability and rear-wheel all-terrain performance
- Adjustable dampening, independent wheel suspension that provides a smooth ride, even over obstacles
- PosiDrive™ technology increases the overall strength of the drive train
- Optional LED headlight, blinker and tail light package for safety
- Painted frame available in 23 different color options



Seating Options

Rehab Seat

- TRAX System with easy dovetail track adjustments of the seat and back
- Extensive seating and positioning options
- Articulating vent tray option

Power Recline Seat

- · Wide range of seating and positioning options
- Low seat to floor options with and without Power CG Tilt
- Headrest design is easily accessed and does not require tools for removal



Power Options

- 53° of Power CG Tilt for optimized positioning
- Power Recline with Power Shear Reduction
- Power Elevating Legrests with Articulation

Quickie S-6 Series Specifications

SPECIFICATIONS	S-636 BC	S-636 SC	S-636 MPC	S-646 SE BD	S-646 SE SD	S-646 SE MPD
HCPCS Code	K0848	K0856	K0861	K0868	K0877	K0884
Drive Wheel Position	RWD	RWD	RWD	RWD	RWD	RWD
Speed	6.5 MPH*	6.5 MPH*	6.5 MPH**	8.5 MPH	8.5 MPH	8.5 MPH
Overall Weight	128 lbs. w/o batteries					
Overall Width	27.75"	27.75"	27.75"	25.75"	25.75"	25.75"
Overall Length	33.5"	33.5"	33.5"	33.5"	33.5"	33.5"
User Weight Capacity	300 lbs.					
Seat Widths	14" to 24"					
Seat Depths	14" to 22"					
Front Seat To Floor Height	18.5" to 20.5"	18.5" to 20.5"	18.5" to 20.5"	18" to 21"	18.5" to 20.5"	18.5" to 20.5"
Seating Frame Options	Rehab	Rehab or Rehab Recline	Rehab Recline	Rehab	Rehab or Rehab Recline	Rehab Recline
Power Seating Options	N/A	Til or Recline	Tilt and Recline	N/A	Tilt or Recline	Tilt and Recline

^{*} Optional 5 mph and 8.5 mph motor packages also available

^{**} Optional 8.5 mph motor package also available

The powerful and compact Quickie P-222 SE is fast, simple, and extremely maneuverable indoors and out and features a quick-release power pack and optional manual conversion kit for convenience and transportability.

QUICKIE P-222 SE



Available in Two Group 4 Models:

- Quickie P-222 SE BD (K0868): No power option P-222 SE base with Rehab seat
- Quickie P-222 SE SD (K0877): Single power option (tilt) P-222 SE base with Rehab seat



Fast and Maneuverable Base

- Linix 8.5 mph, 4-pole standard motor package
- PosiDrive[™] technology increases the overall strength of the drive train and features easy-to-service hubs
- · 26" turning radius for excellent maneuverability
- 4" curb climbing capability



Seating and Power Options

Rehab Seat

- Simple seating and positioning options mix
- · Swing-away and fixed hanger options
- Optional 53° of CG tilt to optimize positioning



Style Options

- Optional manual wheelchair conversion kit for user self propulsion
- Optional LED light package includes headlights, blinkers and tail light for safety
- Painted frame available in 23 different color options

Quickie P-222 SE Specifications

SPECIFICATIONS	P-222 SE BD	P-222 SE SD
HCPCS Code	K0868	K0877
Drive Wheel Position	RWD	RWD
Speed	8.5 MPH	8.5 MPH
Overall Weight	115 lbs. w/o batteries	115 lbs. w/o batteries
Overall Width	24.5"	24.5"
Overall Length	31.5" w/o footplates	31.5" w/o footplates
User Weight Capacity	350 lbs.	350 lbs.
Seat Widths	14" to 24"	14" to 24"
Seat Depths	14" to 20"	14" to 20"
Front Seat To Floor Height	18" to 20"	17.5" to 20.5"
Seating Frame Options	Rehab	Rehab
Power Seating Options	N/A	Tilt

PG Drives Technology

Option availability varies by chair and model. Please see order form for detailed configuration information.





Switch-It Head Array (adult or pediatric)

VR2 Non-Expandable Controls

- Industry standard non-expandable electronics
- Dependable, highly flexible, and simple to use
- · 4-way toggle switch for operation of tilt and power legrests without the need for expandable controls
- Optional Attendant Control for operation by caregiver

R-net Expandable Controls

- 8 uniquely programmable profiles for easy transitions between environments
- Assignable buttons for convenient control of common functions
- Versatile joystick options
- Expandable LED joystick
- Joystick w/ Color display
 - Color Screen for clear operation of functions
 - On-board programming capabilities
 - Available with mono and stereo jacks for adding external actuator and ON/OFF switch control
 - Available with Toggle, Speed Potentiometer, and stereo jacks for quad-friendly controls
- OMNI Input Control Module
 - Infra Red (IR) functions for operation of IR controlled devices such as TVs and DVD players
 - Bluetooth Mouse-Mover for PC mouse control
 - On-board programming capabilities
- Full specialty control and switch input capabilities
- · Optional Attendant Control for operation by caregiver

Back Upholstery Options



QUICKIE® Tension Adjustable Upholstery

- Available with Ballistic Nylon or 3DX Microclimatic fabric
- 1" width adjustment



, ,

SPOT Curved Back

- Solid Support
- Optional preassembled Whitmyer headrests
- Optional AES positioning components



JAY® J3 Backrest

- Two-point or four-point quick-release hardware
- Range of back heights and contours to meet user needs
- Can mount Whitmyer headrests or lateral positioning supports



SPO Backrest

- JAY or ART SPO Backrests are designed for the unique needs of a client in power tilt.
- Provides postural management in a package that can be customized in the field.
- Shape, height, width and thickness of the foam customizable by user.
- ART SPO Back offers custom shapes: i-back, scapular cut-out and custom rectangular.

Base Options & Accessories

Option availability varies by chair and model. Please see order form for detailed configuration information.







4-Point Transit Tie-Downs



Articulating Vent Tray



Fixed Vent Tray



Gp 24 Batteries with Std Posts



Gp 24 Batteries with Flat Tops



22NF Batteries with Std Posts







8A Dual Mode (Off-Board) CTE



Tuffak Tray Table



Black Utility Backpack



Black/Charcoal Kid's Backpack



Auto Style Buckle



Belt 2" Aircraft Buckle



Belt 2" Aircraft Buckle Padded







Walker Holder

Armrests

Option availability varies by chair and model. Please see order form for detailed configuration information.



Dual Post Flip Back Height Adjustable



Flip Back



Standard Cantilever with 2 Point Locking Post



Standard Cantilever



Low Cantilever



Standard Single Post



Reclining Standard Height



Cantilever Reclining

Armpads



Waterfall Armpad



Standard Armpad



Reclining Armpad



Ottobock® Reclining Armpad



Ottobock® Flat Hand Pad

Positioning Options



Whitmyer® Head Supports



Lateral Thoracic Supports



Long Thigh Support with mesh pocket



Swing-Away Knee Adductor



Chest Strap

Legrests

Option availability varies by chair and model. Please see order form for detailed configuration information.



65° Swing-Away



70° Swing-Away



75° Tapered Swing-Away



90° Swing-Away



Manual ELR Swing-Away



Fixed Center Mount



Centermount Power ELR with Articulation



Swing Away Power ELR with Articuation

Footplates



Composite with Heel Loop



Adult Angle Adjust with Heel Loop



Kids Angle Adjust with Leg Strap



Aluminum



One Piece Angle Adjust Footplate



Centermount Single Footplate



Centermount Dual Footplate



Centermount High Mnt Footplate



Centermount Single/Dual Footplate

Electronics

Option availability varies by chair and model. Please see order form for detailed configuration information.



VR2 Non-Expandable Controller



R-net Expandable Controller



R-net Environmental Control Output Module (ECM)



R-net Bluetooth® Mousemover

Joysticks



Non-expandable **VR-2 Joystick**



R-net Expandable **LED** Joystick



Joystick w/Stereo Jacks & Color Display



Joystick w/Toggle, Speed **Potentiometer, Stereo Jacks** & Color Display



R-net OMNI Input Control Module



Fixed



Swing-Away





Joystick Handles



Ball



Foam Ball



T-Handle



Goalpost

Programmers



VR-2 Hand Held Programmer



R-net PC Programmer



DTT VR2 and R-net



Ribbon Switch



Buddy Button Switch



Disc Switch



Wobble Switch



Micro Light Switch



Egg Switch-Black



Stereo to 2 Mono Splitter

Specialty Drive Control Options



Quickie Sip n Puff



ASL Mini Proportional Joystick Chin/Lip Package



ASL Head Array (adult or pediatric)



ASL Proportional Mini Joystick Midline with Gatlin Package



Switch-It Head Array (adult or pediatric)



Quickie Proportional Chin Control



www.built4me.us

Product Customizations

The Quickie Built-4-Me group is dedicated to providing individual design solutions not available through our customary production channels. Built-4-Me will listen to your specific requests for Quickie products, then design and manufacture the product to meet the individual's custom needs or cosmetic desires.

Featured Power Chair Customizations

- 24" Seat width on QM-715 HD
- Captain's Seat on QM-710

Seating Selection







SUNRISE Customer Service: 800.333.4000 www.SunriseMedical.com