


DUPONT™ TYVEK® MICRO-CLEAN® 2-1-2 CC252B OPTION 0S

GARMENT TECHNICAL DATA SHEET



This picture is for measurement reference only.

Customer Service:

North America 1-800-931-3456

SafeSPEC™ Home Page

Seams and closures have less barrier than fabric. Note: for protection from hazardous or infectious liquids, additional barrier tests are required to establish suitability for use. CAUTION: This information is based upor technical data that DuPont believes to be reliable. It is subject to revision as additional knowledge and experience are gained. DuPont makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics, not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under the specific end-use conditions, at their own discretion and risk Anyone intending to use this information should first verify that the garment selected is suitable for intended use. In many cases, seams and closures may provide less barrier than the fabric. If the fabric becomes torn, abraded, or punctured, end-user should discontinue use of garment to avoid compromis. the barrier protection. SINCE CONDITIONS OF USE ARE OUTSIDE OUR CONTROL. WE MAKE NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING WITHOUT LIMITATION NO WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE AND ASSUME NO LIABILITY IN CONNECTION WITH ANY OF THIS INFORMATION. This information is not intended as a license to operate under or a recommendation to infringe any patent, trademark or technical information of DuPont of others covering any material or its use. Data presented does not comprise a product specification

Warning: Cleanroom apparel should not be used around heat, flames, sparks or in potentially flammable or explosive environments. Cleanroom fabrics should have slip-resistant materials on the outer sole of boots, shoe covers, or other garment surfaces in conditions where slipping could occur.

Silicone Statement: In the past, DuPont has found that threads and zippers can be the most significant source of silicone oil contamination in garments. DuPont specifies that thread and zippers used in DuPontTh Tyvek® IsoClean® and ProClean® garments be manufactured without the use of silicone oils. For end uses with concerns about contamination with silicone oils or any other contaminants, the best practice is to audit inbound materials, including garments, for those contaminants.

Latex Statement: As of January 1, 2006, DuPont production specifications exclude use of components containing natural rubber latex in the manufacture of DuPontTM Tyvek® IsoClean® and ProClean® garments. Anyone who begins to exhibit allergic response during the use of DuPont products should immediately cease using these products. The incident should also be reported to DuPont at 1.800.441.3637.

Measurements are approximate values intended to assist in proper size selection. Normal variability may result in slight differences in actual garment sizes.

 $\textit{Copyright} @ \textit{2019 DuPont de Nemours Inc. All rights reserved. The DuPont Oval Logo, DuPont} ^{\text{TM}}, \textit{and all topology} \\$ products denoted with ® or ™ are trademarks or registered trademarks of DuPont or its affiliates. Printed

PRODUCT INFORMATION

ATTRIBUTES

DuPont™ Tyvek® Micro-Clean® 2-1-2. Coverall. Bound seams. Bound Neck with Loop at Center Back. Dolman Sleeve Design. Covered Elastic Wrists and Ankles. Zipper Closure. Blue

Certificates of Sterility Available Here

CATALOG NUMBER

CC252BBUxx0025yy (xx=size) ?

PHYSICAL PROPERTIES - FARRIC DATA

FULL PART NUMBER	FABRIC OR MATERIALS	DESIGN	SEAM	COLOR	QUANTITY/BOX	SIZES	OPTION CODES
CC252BBU							

Tyvek® SM, MD, xx0025yy (Micro-Clean®Coverall (all) Bound Blue 25 per case LG, XL, 2X, xx=size) 3X. 4X. 5X

TYPICAL	FINISHED DIMI	ENSIONS	,		
SIZE	SLEEVE LENGTH	CHEST WIDTH	INSEAM	FITS CHEST	FITS HEIGHT
SM	35	22 3/4	28 3/4	32 1/4 - 35 3/4	5'0" - 5'7"
MD	35 3/4	23 3/4	29	34 1/4 - 37 3/4	5'3" - 5'7"
LG	36 1/4	24 1/2	30 1/4	35 3/4 - 39 1/4	5'5" - 5'9"
XL	36 3/4	26 1/2	30 1/4	39 3/4 - 43 1/4	5'8" - 6'2"
2X	37 3/4	28 1/2	30 3/4	43 3/4 - 47 1/4	6'0" - 6'4"
3X	46 1/4	30 1/2	34 3/4	47 3/4 - 51 1/4	6'2" - 6'4"
4X	47 1/4	32 1/2	36	51 3/4 - 55 1/4	6'4" - 6'7"
5X	47 1/4	40 1/2	36 1/2	67 3/4 - 71 1/4	6'7" - 6'10"

FIT SICAL FROF LIKTLES - LABRIC DATA Typical values, not specifical						
	PROPERTY	TEST METHOD	TYPICAL RESULT	STDDEV		
	Basis Weight	ASTM D3776	1.3 oz/yd ²	0.16 oz/yd ²		
	Breaking Strength - Grab (MD)	ASTM D5034	18 lb _f	2 lb _f		
	Breaking Strength - Grab (CD)	ASTM D5034	17 lb _f	1 lb _f		
	Surface Resistivity (25°C / 55& RH)	ASTM D257	1 x 10^10 ohms/square	е		
	Bacterial Filtration Efficiency (3.0 micron)	ASTM F2101	98.8 %	0.7 %		
	Hydrostatic Head	AATCC 127	19 in H ₂ O	2 in H ₂ O		
	Wearing Apparel Flammability	16 CFR 1610	Class 1			