

SILICONE CASTING RUBBERS

"Dedicated to QUALITY, SERVICE, SAFETY, and INNOVATION"

TC-5110 A/B 10 SHORE A TRANSLUCENT SILICONE RUBBER

TC-5110 A/B is a room temperature, addition/platinum curing silicone rubber designed for making molds and parts. Featuring exceptional tear strength, low viscosity, 1:1 mix ratio, and a quick demold time, this system is user friendly while producing high quality finished products. When used to make molds, the TC-5110 A/B is translucent enough to see through when casting into the mold cavity. For making parts, this system is easily pigmented with silicone pigments. This product has been successfully tested for skin safety and cytotoxicity by an independent lab (results are available upon request).

- High Tear Strength
- Translucent/Easily Pigmented
- Cures at ambient temperatures
- Tested for Skin Safety

- Medical Simulations
- Props for Movie Special FX
- Flexible Molds
- Tested for Cytotoxicity

PHYSICAL PROPERTIES	TEST METHOD	RESULTS	
Hardness, Shore A	ASTM D 2240-04e1	10 ± 5	
Density (g/cc)	ASTM D 792-00	1.109	
Cubic Inches per Pound	N/A	25.1	
Color/Appearance	Visual	Colorless/Translucent	
Tensile Strength (psi)	ASTM D412-98a(2002)e1	600	
Tensile Modulus (psi)	ASTM D412-98a(2002)e1	150	
Elongation (%)	ASTM D412-98a(2002)e1	620	
Tear Strength (pli)	ASTM D 624-00e1 Die B	135	
Shrinkage (in/in) linear	ASTM D2566 @ 1" depth	Nil	
Dielectric Constant, 1 MHz	ASTM D150-87	3.191	
Dissipation Factor, 1 MHz	ASTM D150-87	0.0049	

^{*}Note: Reported physical properties are based on test specimens cured 48 hours at room temperature.

HANDLING PROPERTIES	Part A	Part B	
Mix Ratio by weight	100	100	
Mix Ration by volume	100	100	
Specific Gravity @ 77°F (25°C)	1.106	1.102	
Color	Colorless	Colorless	
Viscosity (cps) @ 77°F (25°C) Brookfield	4,600	3,600	
Mixed Viscosity (cps) @ 77°F (25°C) Brookfield	2,500		
Work Time, 100g mass @ 77°F (25°C)	30 – 40 minutes		
Gel Time	50 – 60 minutes		
Demold Time @ 77°F (25°C)	2 – 3 hours		

Properties above are typical and not for specifications.

Date: 12/04/2020

INHIBITION:

Certain materials will cause inhibition or neutralization of the curing agent. These materials include condensation/tin cured based silicone, lacquer and enamel coatings, polyester-based products, copper or copper containing metals, some SLA 3D Printing resins, and natural rubbers like latex. Inhibition may easily be determined by brushing a small quantity of TC-5110 A/B over a localized area of the surface to be reproduced. If the TC-5110 A/B is tacky or uncured after the cure time, then you know the mold surface is acting as an inhibitor. To insure against possible problems, it is advisable to spray a barrier film over any questionable surfaces. This is the best way of treating clays and other surfaces that cause inhibition. Contact BJB for recommended products.

STORAGE:

Store ambient temperatures, 65-80°F (18-27°C). Unopened containers will have a shelf life of 12 months from date of shipment when properly stored at recommended temperatures. Purge opened containers with dry nitrogen before re-sealing.

PACKAGING	Part A	Part B	Cubic Inches per Kit
Pint Kits	1 lb.	1 lb.	50
Quart Kits	2 lbs.	2 lbs.	100
Gallon Kits	8 lbs.	8 lbs.	402
5-Gallon Kits	40 lbs.	40 lbs.	2,008
55-Gallon Drum Kits	440 lbs.	440 lbs.	22,088

SAFETY PRECAUTIONS:

Use in a well-ventilated area. Avoid contact with skin using protective gloves and protective clothing. Repeated or prolonged contact on the skin may cause an allergic reaction. Eye protection is extremely important. Always use approved safety glasses or goggles when handling this product.

IF CONTACT OCCURS:

Skin: Immediately wash with soap and water. Remove contaminated clothing and launder before reuse. It is not

recommended to remove resin from skin with solvents. Solvents only increase contact and dry skin. Seek qualified

medical attention if allergic reactions occur.

Eyes: Immediately flush with water for at least 15 minutes. Call a physician.

Ingestion: If swallowed, call a physician immediately. Remove stomach contents by gastric suction or induce vomiting only

as directed by medical personnel. Never give anything by mouth to an unconscious person.

Refer to the Material Safety Data Sheet before using this product.



Silicone Handling Guide

Date: 12/04/2020

Date: 12/04/2020