





[Click Here for Brochure](#)

Smart Gaskets® value is proven when validating sterility in a high-purity pharmaceutical system. Each seal requires a specifically designed thermocouple clamp but easily installs in between any ASME BPE or standard tri-clamp.



EPDM Smart Gasket®

| | |
|--------------|--|
| Size | 0.5" to 4" |
| Temp Range | - 34°C to 148°C |
| Applications | Process Validation, Thermal Mapping & In-line Sampling |
| Material | EPDM |
| Pack Size | Individual or Multiples |
| Colours | Black (Standard) |
| Options | Laser Engraving |



Certificates Available

FDA



ADI

USP VI

Available Sizes

| Part Number | Size | Port | Gasket O.D. | Gasket I.D. | Bead |
|--------------|-------|------|-------------|-------------|--------|
| G-TH-050-E-1 | 0.5" | 1 | 0.86" | 0.38" | NA |
| G-TH-050-E-2 | 0.5" | 2 | 0.86" | 0.38" | NA |
| G-TH-050-E-3 | 0.5" | 3 | 0.86" | 0.38" | NA |
| G-TH-050-E-4 | 0.5" | 4 | 0.86" | 0.38" | NA |
| G-TH-075-E-1 | 0.75" | 1 | 0.86" | 0.62" | NA |
| G-TH-075-E-2 | 0.75" | 2 | 0.86" | 0.62" | NA |
| G-TH-075-E-3 | 0.75" | 3 | 0.86" | 0.62" | NA |
| G-TH-075-E-4 | 0.75" | 4 | 0.86" | 0.62" | NA |
| G-TH-100-E-1 | 1" | 1 | 1.984" | 0.9" | 1.718" |
| G-TH-100-E-2 | 1" | 2 | 1.984" | 0.9" | 1.718" |
| G-TH-100-E-3 | 1" | 3 | 1.984" | 0.9" | 1.718" |
| G-TH-100-E-4 | 1" | 4 | 1.984" | 0.9" | 1.718" |
| G-TH-150-E-1 | 1.5" | 1 | 1.984" | 1.4" | 1.718" |
| G-TH-150-E-2 | 1.5" | 2 | 1.984" | 1.4" | 1.718" |
| G-TH-150-E-3 | 1.5" | 3 | 1.984" | 1.4" | 1.718" |
| G-TH-150-E-4 | 1.5" | 4 | 1.984" | 1.4" | 1.718" |
| G-TH-200-E-1 | 2" | 1 | 2.515" | 1.9" | 2.218" |
| G-TH-200-E-2 | 2" | 2 | 2.515" | 1.9" | 2.218" |
| G-TH-200-E-3 | 2" | 3 | 2.515" | 1.9" | 2.218" |
| G-TH-200-E-4 | 2" | 4 | 2.515" | 1.9" | 2.218" |
| G-TH-250-E-4 | 2.5" | 1 | 3.05" | 2.4" | 2.781" |
| G-TH-250-E-4 | 2.5" | 2 | 3.05" | 2.4" | 2.781" |
| G-TH-250-E-4 | 2.5" | 3 | 3.05" | 2.4" | 2.781" |
| G-TH-250-E-4 | 2.5" | 4 | 3.05" | 2.4" | 2.781" |
| G-TH-300-E-1 | 3" | 1 | 3.579" | 2.9" | 3.281" |
| G-TH-300-E-2 | 3" | 2 | 3.579" | 2.9" | 3.281" |
| G-TH-300-E-3 | 3" | 3 | 3.579" | 2.9" | 3.281" |
| G-TH-300-E-4 | 3" | 4 | 3.579" | 2.9" | 3.281" |
| G-TH-400-E-1 | 4" | 1 | 4.682" | 3.869" | 4.344" |
| G-TH-400-E-2 | 4" | 2 | 4.682" | 3.869" | 4.344" |
| G-TH-400-E-3 | 4" | 3 | 4.682" | 3.869" | 4.344" |
| G-TH-400-E-4 | 4" | 4 | 4.682" | 3.869" | 4.344" |

