

# CERTIFICATE OF QUALITY

# EZwaste<sup>®</sup> Solvent Waste

Catalog Number:

Lot Number:

Description: EZwaste<sup>®</sup>

Date of Manufacture:

### Materials of Construction:

- Chemical Exhaust Filter: Polypropylene housing with activated carbon filter
- VersaCap: Polypropylene with EPDM gasket
- Manifold Adapter: Delrin
- Carboy: High-Density Polyethylene (HDPE)
- Fittings:
  - 1/4-28 Male Nut & Plug – Delrin
  - Ferrule for 1/8" & 1/16"
  - 1/2-20 Male Nut & Ferrule
  - 1/2-20 UNF Plug – HDPE
  - 1/4" MNPT fitting & Plug – Polypropylene
  - 1/8" MNPT HB Plug – Polypropylene

### Filter Replacement Schedule

At a typical analytical flow rate of 1 mL/min at Standard Temperature and Pressure (STP)

- For Normal Phase Solvent: Replace chemical exhaust filter every 20-30 days
- For Reverse Phase Solvent: Replace every 3-4 months

### Disposal

Always dispose of saturated filters in accordance with local regulations and safety codes

### ISO 9001 Quality Standard:

This product was assembled in a facility whose Quality Management System is approved by an accredited registering body to the appropriate ISO 9001 Quality Systems Standard.

### ISO 13485 Quality Standard:

This product was assembled in a facility whose Quality Management System is approved by an accredited registering body to the appropriate ISO 13485 Quality Systems Standard.



*Brian J. Abbott*

Manager, Regulatory Affairs and QA