

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SmartPro 120V 1kVA 750W Medical-Grade Line-Interactive Tower UPS with 4 Outlets, Full Isolation, USB, Lithium Battery

MODEL NUMBER: SMART1200XLHGL







Provides UL 60601-1 compliant, medical-grade 1kVA/750W power backup, ideal for use in patient-care vicinities. Lithium Iron Phosphate batteries provide 20–30 times the cycle life of traditional batteries.

Description

Tripp Lite's SMART1200XLHGL medical-grade UPS system provides dependable lithium iron phosphate (LiFePO4) battery backup, so you can work through short power failures and perform an orderly system shutdown in a prolonged blackout. It's fully compliant with UL 60601-1 regulations when plugged into a hospital-grade outlet, making it ideal for use in patient-care vicinities. The 1kVA/750W capacity provides up to 28 minutes of runtime for a half load and 10 minutes for a full load.

Built-in line-interactive voltage regulation corrects brownouts as low as 81V and overvoltages as high as 143V to normal 120V nominal output, without drawing battery power. A built-in isolation transformer with Faraday shield offers full isolation and removes common mode noise while maintaining full AC surge suppression in all modes. It also reduces the cumulative leakage current of connected equipment to less than 100 A. Floating AC output prevents noise coupling from noisy hospital ground systems.

This UPS system features four NEMA 5-15R-HG hospital-grade outlets and has a hospital-grade NEMA 5-15P-HG plug with a six-foot cord for flexibility in placement. All four outlets provide both backup protection and 940 joules of surge protection.

The SMART1200XLHGL also features diagnostic LEDs, as well as a USB port and a DB9 serial port that work with Tripp Lite's free downloadable PowerAlert® software for safe, unattended system shutdown and file saves in the event of a prolonged power failure.

Features

Provides Ideal UPS Backup in Healthcare FacilitiesCompliant with UL 60601-1 standards for use in patient-care vicinities when plugged into a hospital-grade outletBuilt-in isolation transformer with Faraday shield offers full isolation and reduces cumulative leakage current of connected equipment to less than 100 AHospital-grade NEMA 5-15P-HG plug with 6 ft. cord provides flexibility in placement Battery Backup and Full Surge ProtectionSupports half load for 28 min. and full load for 10 min. with standard LiFePO4 internal batteryHospital-grade NEMA 5-15R-HG outlets provide 940 joules of surge protectionEMI/RFI noise filtering ensures equipment runs smoothly without line noise interferenceResistant to electrostatic discharge10,000-cycle LiFePO4 battery

LEDs and Audible Alarms Keep You Aware of Power Status Indicator lights monitor when the UPS is

Highlights

- 28 min. runtime at half load; 10 min. at full load
- Reduces cumulative leakage current to under 100 A
- Approved for use within the Patient Care Vicinity
- Approved to EN60601-1-2:2015
 IEC60601-1-2:2014, 4th
 Edition
- 940 joules of surge protection
- 10,000-cycle LiFePO4 battery

Package Includes

- SMART1200XLHGL 1kVA/750W Medical-Grade Tower UPS System
- USB monitoring cable, 6 ft.
- DB9 serial monitoring cable, 6 ft.
- 5 yr. warranty on UPS and batteries
- Owner's manual



on and supplying utility power, when operating in voltage correction mode or in battery mode, relative load level and low-battery warningAudible alarms alert you to power failure, overload and low battery conditionsMute/quiet mode ensures "alarm fatigue" compliance

Saves Your Files, Even When You're AwayWorks with Tripp Lite PowerAlert software (available as a free download) to enable safe, unattended system shutdown and files saves during prolonged power failuresConnects to your computer via DB9 or USB port

Specifications

| OVERVIEW | | |
|--|-----------------------------------|--|
| UPC Code | 037332192202 | |
| UPS Type | Line-Interactive | |
| INPUT | | |
| Rated input current (Maximum Load) | 9.2A | |
| Nominal Input Voltage(s) Supported | 120V AC | |
| UPS Input Connection Type | 5-15P-HG | |
| Input Circuit Breakers | 15A | |
| UPS Input Cord Length (ft.) | 6 | |
| UPS Input Cord Length (m) | 1.8 | |
| Recommended Electrical Service | 15A 120V | |
| Input Phase | Single-Phase | |
| Input Cord Length (ft.) | 6 | |
| Input Cord Length (m) | 1.83 | |
| OUTPUT | | |
| Output Volt Amp Capacity (VA) | 1000 | |
| Output kVA Capacity (kVA) | 1 | |
| Output Watt Capacity (Watts) | 750 | |
| Power Factor | 0.8 | |
| Frequency Compatibility | 60 Hz | |
| Output Voltage Regulation (Line Mode) | -18%, +8% | |
| Output Voltage Regulation (Battery Mode) | 115V (+/- 5%) | |
| Output Receptacle Details | Hospital grade output receptacles | |
| Output AC Waveform (AC Mode) | Sine wave | |
| Output AC Waveform (Battery Mode) | PWM sine wave | |





| N . 10 | | | |
|--|---|--|--|
| Nominal Output Voltage(s) Supported | 115V; 120V | | |
| Output Receptacles | (4) 5-15R | | |
| Individually Controllable Load Banks | No | | |
| BATTERY | | | |
| Battery Type | Lithium Ion | | |
| Full Load Runtime (min.) | 10 min. (750w) | | |
| Half Load Runtime (min.) | 28 min. (375w) | | |
| Expandable Runtime | No | | |
| DC System Voltage (VDC) | 36 | | |
| Battery Recharge Rate (Included Batteries) | Less than 4.5 hours from 10% to 90% | | |
| Battery Access | Battery access door | | |
| Internal UPS Replacement Battery Cartridge | RBC53L | | |
| VOLTAGE REGULATION | | | |
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 81 to 143 | | |
| Overvoltage Correction | Input voltages between 126 and 143 are reduced by 9% | | |
| Undervoltage Correction | Input voltages between 96 and 106 are boosted by 10% | | |
| Severe Undervoltage Correction | Input voltages between 81 and 95 are boosted by 21% | | |
| USER INTERFACE, ALERTS & CONTROLS | | | |
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation | | |
| Alarm Cancel Operation | Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status | | |
| Audible Alarm | Factory-muted audible alarm indicates power-failure, overload and low-battery conditions | | |
| LED Indicators | 5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status | | |
| SURGE / NOISE SUPPRESSION | | | |
| UPS AC Suppression Joule Rating | 940 | | |
| UPS AC Suppression Response Time | Instantaneous | | |
| EMI / RFI AC Noise Suppression | Yes | | |
| AC Suppression Joule Rating | 940 | | |
| ISOLATION | | | |
| Output Isolation Transformer | Hospital grade load isolation transformer | | |
| Leakage Current | Less than 100 microamps | | |



| PHYSICAL | | |
|---|---|--|
| Cooling Method | Fan | |
| Installation Form Factors Supported with Included Accessories | Tower | |
| Installation Form Factors Supported with Optional Accessories | Wallmount (UPSWM - tower mounting kit) | |
| Primary Form Factor | Tower | |
| Primary UPS Depth (mm) | 241 | |
| Primary UPS Height (mm) | 318 | |
| Primary UPS Width (mm) | 191 | |
| Shipping Dimensions (hwd / cm) | 43.18 x 28.96 x 33.27 | |
| Shipping Dimensions (hwd / in.) | 17.00 x 11.40 x 13.10 | |
| Shipping Weight (kg) | 16.57 | |
| Shipping Weight (lbs.) | 36.54 | |
| UPS Housing Material | PVC | |
| UPS Power Module Dimensions (hwd, cm) | 31.75 x 19.05 x 24.13 | |
| UPS Power Module Dimensions (hwd, in.) | 12.5 x 7.5 x 9.5 | |
| UPS Power Module Weight (kg) | 15.24 | |
| UPS Power Module Weight (lbs.) | 33.6 | |
| ENVIRONMENTAL | | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius | |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius | |
| Relative Humidity | 0 to 95%, non-condensing | |
| AC Mode BTU / Hr. (Full Load) | 162.8 | |
| Battery Mode BTU / Hr. (Full Load) | 315.2 | |
| AC Mode Efficiency Rating (100% Load) | 94% | |
| COMMUNICATIONS | | |
| Network Monitoring Port Description | Supports detailed monitoring of UPS and site power conditions | |
| PowerAlert Software | For local monitoring via the UPS's built-in communication ports , download PowerAlert Local software at http://www.tripplite.com/poweralert | |
| Communications Cable | USB and DB9 serial cabling included | |
| | USB; DB9 Serial | |



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

| Transfer Time | 2-4 milliseconds | |
|---|---|--|
| Low Voltage Transfer to Battery Power (Setpoint) | 81 | |
| High Voltage Transfer to Battery Power (Setpoint) | 143 | |
| SPECIAL FEATURES | | |
| Grounding Lug | Grounding lug (equipotential) | |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported | |
| High Availability UPS Features | Hot swappable batteries | |
| STANDARDS & COMPLIANCE | | |
| UPS Certifications | Tested to UL1778 (USA); Tested to CSA (Canada); Meets FCC Part 15 Category A (EMI); Tested to UL60601-1 (medical grade) | |
| WARRANTY | | |
| Product Warranty Period (Worldwide) | 5-year limited warranty | |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies