

The thinnest butyl glove providing the best resistance to the most aggressive chemicals with dexterity and comfort

- The glove provides the best resistance to the most aggressive chemicals, without compromising dexterity or comfort.
- Flexible and excellent dexterity, designed for comfort with a natural, curved ergonomic shape and soft feel.



Industries

- Automotive
- Life Sciences
- Chemical

Applications

- Equipment repair & maintenance
- Loading and unloading of process equipment
- Handling incoming goods
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Charging and blending raw materials
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process
- Unexpected leakages spills or other releases

Key Features

- 38-514 offers superior protection against aldehydes, ketones and esters as well as concentrated mineral acids
- The glove is very flexible and provides excellent dexterity
- Designed for comfort, with a natural, curved ergonomic shape and soft feel, they offer easy donning and good grip
- The absence of latex proteins means there's no risk of latex allergies
- Rough finish on the hand section of the glove for safer handling



Performance Standards



CHEMICAL AGENT	BREAKTHROUGH TIME
Methanol (A)	>480
Acetone (B)	337
Acetonitrile (C)	>480
Ethyl acetate (I)	55
Sodium hydroxide, 40 % (K)	>480
Nitric acid, 65% (M)	>480
Hydrogen peroxide, 30 % (P)	>480
Hydrofluoric acid, 40% (S)	>480
Formaldehyde, 37 % (T)	>480

PERMEATION BREAKTHROUGH TIMES ACCORDING TO EN 16523-1 : 2015 (MINUTES)						
0	1	2	3	4	5	6
< 10	10-30	30-60	60-120	120-240	240-480	> 480
Not recommended	Splash protection		Medium protection		High protection	

Data given in the table above are based on results of laboratory tests performed on the palm area of the glove. These tests were run using standard test methods that may not adequately replicate any specific conditions of end use. Because Ansell has no detailed knowledge or control over the conditions of end use, any of these data must be advisory only, and Ansell must decline any liability.

Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 38-514	Butyl Polymer,	7, 8, 9, 10, 11	350 mm, 14 inches	Black	<ul style="list-style-type: none"> • 36 pairs in a carton; individually wrapped with insert • Size 11 unavailable in Canada and USA

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
Q7001 Torre II,
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2018 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.