
† VALIANT

FIR517 Decorative Log Storage Rack Instructions

Contents

- 2 x main frame
- 5 x connecting bars
- 10 x screws
- 1 x hex key





5 x connecting bars



10 x screws



Guidance notes

- Do not overtighten screws finger tight only.
- Take care when placing on Shiny or delicate flooring – Place on a mat or fit furniture pads.
- Place the stand a safe distance from the fire or stove.

Assembly

- Loosely fit the Storage Rack together using the diagram as a guide.
- Place upright on a level surface and tighten all screws.
- The Storage Rack is now ready for use.

Storing Logs

- Place split logs in the store and allow them to season fully naturally in all weathers, rain and shine.
- Allow 12 months for freshly felled and split logs to fully season.


Your log rack is steel, painted to give years of use, reliable storage and seasoning capacity.

Burning Logs

- Remember that burning fully dried logs will give off more heat and produce fewer emissions than unseasoned logs.
- Before burning, ensure logs are below 20% moisture content by using a Valiant Moisture Meter.

Warranty

This product is guaranteed by Accessory Outlet for a period of 1 year from the date of purchase under a Limited Warranty Agreement. During this period if there is a defect due to faulty materials or workmanship, the retailer from whom you purchased it will replace it with the same or a similar model on production of your purchase receipt or proof of purchase. This guarantee does not cover defects arising from accidental damage, misuse or wear and tear, and is available only to the original purchaser of the product. This does not affect your statutory rights.





Contact

Valiant is a trading name of The Accessory Outlet Ltd.

The helpline is a one-to-one service available between the hours of:

Monday to Friday: 8.30am - 4.30pm Tel: +44 (0) 1763 284181

Email: contact@simplyvaliant.co.uk Website: www.simplyvaliant.co.uk Solution House, Sandon Road, Therfield, Hertfordshire, SG8 9RE To ensure that your call is handled quickly and efficiently, please ensure you have the model number (FIR517) and any other relevant information regarding your product to hand at the time of your call. Please retain these instructions for future use.

