



PT2 - Pression Tamp

Automatic Coffee Tamper

Keeping the cup quality consistent





PT2 - Precision Tamp

Precise and consistent tamping is an essential part of the process to create and maintain great espresso.

The PT2 patent Guide Leveling System (GLS) improves the quality of each coffee bed which then helps eliminate channelling caused from uneven and or inconsistent tamping. The GLS therefore significantly enhances the quality of your espresso.

Simple to use and quick to adjust mid service, the PT2 helps maintain extraction quality as temperature and humidity changes occur throughout the day.

Maintains consistency in changeover shifts between morning to afternoon Baristas. Even over multi venue café sites with upholding the coffee brand itself.

PT2 sits on small footprint maximising working environment bench space.

Other features include: Low voltage - PT2 operates on only 12v, Sleep Mode, Total Tamp Counter, Segmented Multi Tamping, Sturdy Nonslip suction cup base.

PRESSURE CONTROL

Create ideal tamping pressures ranging from 2kg to 38kg

PRECISE AND CONSISTANT PRESSURE

Accurate pressure no matter the amount of coffee or grind size.

FLAT SURFACE

Patent GLS – Guide Levelling System ensures a flat coffee bed every time.

NON-STICK COATING

Nano Technology with food grade safe non-stick coating ensures clean tamping.

CAST ALLOY STRUCTURE WITH ALL METAL FEATURES

Strong, Reliable and Durable and Sturdy Nonslip suction cup base





Precise - GLS - Guide Levelling System

CINOART's patent GLS "Guide Leveling System" prevents channelling caused from uneven tamping ensuring the coffee bed is flat every time

GLS upholds cup quality consistency as an uneven coffee bed creates under or over extraction resulting in unwanted flavours.



Precise - Pressure Control

Select the ideal pressure setting for your desired recipe extraction times from between 2kg to 38kg.

Assured pressures are delivered consistently even upon different particle sizes and dosed volumes.

Three programmable multi tamp settings.

Built-in recording function to calculate total usage / cycles.

Easy to adjust and fit a variety of Portafilter handles.



Precise - Segmented Multi Tamping

1: Choose from a single, double, or triple tamps

2: Within each tamp cycle you can set different segmented tamp pressures

Example: 1st Tamp value at 8kg followed by the 2nd Tamp at 30kg of down pressure or any value combination in between 2kg - 38kg





Metal Sensor

Precise - Safety

Group handle detection sensor only activates with metal (not fingers)

Operating on only 12 Volts to the unit via an inline stepdown transformer

Surge protection designed to the main electronic control board ensuring longevity and reliability.

Sturdy Nonslip suction cup base



Precise - Non-Stick Coating

Nano Non-Stick Technology reduces residual build-up of the coffee fines and oils maintaining clean tamping



Precise - Construction

A strong cast alloy housing and all metal features ensures durability and reliability

Easy access for technical servicing



Precise Specifications

Name: Automatic Coffee Tamper

Model: PT2 - Precision Tamp 2

Power: 110~220V 50\60Hz

Voltage: 12V DC

Weight: 3.7kg

Tamp Diameter: 58.3mm / Flat Base

Pressure: from 2kg to 38kg

Cycle Speed: 1.2 Sec

Multi Segment Tamping: 1, 2 or 3 cycles