




PRESTO A80

Temperature Control System / Process System

Reactor temperature control, tests for all kinds of substances or temperature simulation – the new PRESTO are made for highly precise temperature control and rapid temperature changes. Highly efficient components allow extremely fast compensation of exothermic and endothermic reactions. Lab users benefit from high flow rates, constant pressure, and a controlled build-up of pump pressure. Permanent internal monitoring and self-lubricating pumps contribute to the new PRESTO's long service life. The integrated 5.7" industrial touch screen displays all important information clearly and concisely enhancing ease of use considerably.

Your advantages

- For highly precise, external temperature applications
- Rapid heating and cooling
- Wide working temperature ranges without changing fluids
- Highest performance with small footprint
- Space-saving design optimizes space utilization in your lab
- NEW 5,7" industrial color TFT touch screen
- NEW USB (Host und Device)
- NEW Ethernet
- NEW SD-Card slot
- RS232 / optional RS485 / optional Profibus DP
- Stand-by input
- Removable venting grid for simplified removal of dust



- Cool-down time (thermal hl)
- Heat-up time (thermal hl)
- Pump capacity (thermal hl)

Technical Data

Order No.	9420801
Category	Temperature Control PRESTO
Working temperature range (°C)	-80 ... +250
Temperature control	ICC
Temperature stability (°C)	±0.01 ... ±0.05
Setting / display resolution	0.01 °C
Integrated programmer	8x60 steps
Temperature Display	TFT Touchscreen
Heating capacity (kW)	1.8

Cooling capacity (Medium: JULABO Thermal Ethanol)	°C	200	20	0	-20	-40	-60	-80
	kW	1.2	1.2	1.2	1.1	1.1	0.65	0.1
Pump capacity flow rate (l/min)	16 ... 40							
Pump capacity flow pressure (bar)	0.3 ... 1.7							
Pump connections	M24x1.5							
Refrigerant stage 1	R507							
Filling volume refrigerant stage 1 (g)	1140							
Global Warming Potential for R507	3985							
Carbon dioxide equivalent stage 1 (t)	4.543							
Refrigerant stage 2	R23							
Filling volume refrigerant stage 2 (g)	500							
Global Warming Potential for R23	14800							
Carbon dioxide equivalent stage 2 (t)	7.4							
External Pt100 sensor connection	integrated							
Digital interface	RS232, SD memory card, USB, Ethernet, Modbus Optional: RS485, Profibus							
Analog connection input / output	Optional							
Ambient temperature	5 ... 40 °C							
Dimensions W x L x H (cm)	43 x 65 x 126							
Weight (kg)	164							
Sound pressure level (distance 1 m) max. (dBA)	68							
Process volume min. (active heat exchanger volume) liters	3.9 (1.7)							
Internal usable expansion vol. (liters)	5.6							
Classification according to DIN12876-1	Classification III (FL)							
Cooling of compressor	2-stage Air							
Available voltage versions	208V/60Hz (-10/+15%) / 15A / Nema N6-20 Plug 230V/50Hz (+/- 10%) / 13A / UK Plug type BS1363A 230V/50Hz (+/- 10%) / 16A / CEE 7/4 Plug type F							

Characteristics

Display



State-of-the-art display technology

TFT Display for comfortable user guidance, colored display of measurement values, graphs and control options, user-defined views

Operation



Optimal ease of use

Touch screen for direct operation via display



Instructions inside

Help menus and explanations in plain text for all control options, help messages and warning messages



Multilingual user guidance





Language selection for display of control options, notifications and warning messages via touchscreen






Convenience for several users

Administrator level for customizing instrument settings, user levels with limited permissions for fast and safe defined access, password protection, all levels adjustable


Temperature Control





- 
For perfect results
 'Intelligent Cascade Control', automatic & self optimizing adjustment of PID control parameters, temperature stability $\pm 0.01\text{ °C}$... $< \pm 0.2\text{ °C}$
- 
Full control
 'Temperature Control Features', for individual optimization, access to all important control parameters, additional settings for band limit, limits, co-speedfactor etc.
- 
Control from the external application
 External Pt100 sensor connection for precise measurement and control directly in the external application
- 
Highest measuring accuracy
 'Absolute Temperature Calibration' for manual compensation of a temperature difference, 3-point calibration


Refrigeration Technology


- 
Consistent cooling capacity
 Easily removable venting grid for quick and easy cleaning
- 
100 % Cooling capacity
 'Active Cooling Control' for cooling available throughout the entire working temperature range, fast cool-down even at higher temperatures
- 
Energy saving cooling
 Proportional cooling control for automatic adjustment of cooling power or temporary switch-off of compressor as needed to save up to 90 % energy in comparison to unregulated cooling machines


Technical Features


- 
Intelligent pump system
 Reliable and consistent pump capacity, electronically adjustable pump stages or pressure value, automatic adjustment of pump capacity to viscosity

- 
Communication via networks
 For the remote control of instruments via Ethernet networks, full access to all functions of the unit via a networkcapable PC
- 
Intelligent communication
 USB connection for data exchange (e.g. service data) or for wireless remote control via WirelessTEMP®
- 
Data exchange via SD-Card
 For data exchange (e.g. service data) via SD memory card
- 
Connections according to standard
 RS232/RS485 dual-interface for serial data transmission according to EIA-485 industry standard (2-wire bus technology), upgradable with Profibus DP


- 
Comfortable program control
 Integrated programmer for the execution of time and temperature dependant profiles, 8 temperature profiles with 60 steps max., with real time clock

- 
Quiet as a whisper
 Efficient components produce only a minimal sound decibel level


- 
Space-saving footprint
 All connections as well supply and exhaust air are located at the front or rear, no venting grids on the sides, units can be placed close to each other or the application


- 
Continuous operation up to +40 °C
 Robust temperature control instrument, continuous operation even at ambient temperatures of up to +40 °C


- 
Easy transport by one person
 Ergonomic design facilitates moving and positioning by one person


- 
Filling level at a glance
 Backlit indicator for selected pump stages and filling volume

Warning & Safety Functions

- 
Early warning system for high/low temperature limits
 Maximum safety for applications, optical and audible signal when limits are exceeded.

- 
Duplicate safety
 Adjustable high temperature cut-off for internal tank and for integrated expansion vessel

- 
For flammable bath fluid
 Classification III (FL) according to DIN 12876-1

- 
Quick support
 If an error occurs, the integrated Black-Box function permits fast diagnosis by the JULABO service team