



GMA CLASSICCUT™ 120

Standard Aperture

Setting	#/Min	Setting	#/Min
0	0.00	5B	1.28
0A	0.03	6	1.33
0B	0.06	6A	1.38
1	0.14	6B	1.45
1A	0.26	7	1.48
1B	0.34	7A	1.53
2	0.41	7B	1.58
2A	0.53	8	1.63
2B	0.59	8A	1.66
3	0.68	8B	1.71
3A	0.75	9	1.74
3B	0.81	9A	1.78
4	0.89	9B	1.81
4A	0.95	10	1.83
4B	1.03	10A	1.84
5	1.09	10B	1.88
5A	1.22	11	1.89



GMA CLASSICCUT™ 120

Aggressive Aperture

Setting	#/Min	Setting	#/Min
0	0.00	5B	1.67
0A	0.00	6	1.75
0B	0.03	6A	1.83
1	0.09	6B	1.92
1A	0.19	7	2.02
1B	0.29	7A	2.10
2	0.40	7B	2.17
2A	0.50	8	2.26
2B	0.62	8A	2.32
3	0.73	8B	2.38
3A	0.85	9	2.42
3B	0.99	9A	2.46
4	1.10	9B	2.52
4A	1.21	10	2.57
4B	1.32	10A	2.60
5	1.43	10B	2.63
5A	1.55	11	2.64

Orifice	Nozzle	Setting
10	30	2A
12	35	3
13	40	3B
14	40	4
15	40	4B
16	40	5B

Orifice	Nozzle	Setting
10	30	2A
12	35	2B
13	40	3
14	40	3A
15	40	3B
16	40	4A

