



GMA CLASSICCUT™ 80

Standard Aperture

Setting	#/Min	Setting	#/Min
0	0.00	5B	1.14
0A	0.00	6	1.21
0B	0.00	6A	1.24
1	0.08	6B	1.30
1A	0.18	7	1.35
1B	0.27	7A	1.39
2	0.35	7B	1.44
2A	0.44	8	1.48
2B	0.53	8A	1.51
3	0.59	8B	1.54
3A	0.68	9	1.58
3B	0.74	9A	1.63
4	0.83	9B	1.67
4A	0.91	10	1.70
4B	0.94	10A	1.71
5	1.01	10B	1.73
5A	1.08	11	1.77



GMA CLASSICCUT™ 80

Aggressive Aperture

Setting	#/Min	Setting	#/Min
0	0.00	5B	1.65
0A	0.00	6	1.76
0B	0.00	6A	1.85
1	0.11	6B	1.95
1A	0.21	7	2.04
1B	0.31	7A	2.11
2	0.42	7B	2.19
2A	0.54	8	2.24
2B	0.65	8A	2.28
3	0.77	8B	2.37
3A	0.90	9	2.41
3B	1.00	9A	2.44
4	1.14	9B	2.51
4A	1.25	10	2.54
4B	1.37	10A	2.59
5	1.47	10B	2.60
5A	1.59	11	2.62

Orifice	Nozzle	Setting
10	30	2B
12	35	3A
13	40	3B
14	40	4A
15	40	5
16	40	6A

Orifice	Nozzle	Setting
10	30	2A
12	35	2B
13	40	3
14	40	3A
15	40	3B
16	40	4A

