SUPER ANCHOR SAFETY®

6x6 D-Plate Anchors Instruction/Specification Manual 2021

Specifications

Minimum Breaking Strength MBS: 5,000lb(22.5kN) in any direction the load is applied to the top fixture. **Proof Loading:** Must not exceed 2,500lb(11.3kN).

4-1 Design Load: 1,250lb(567kg).

Service Load: 360°

Low Temperature: -30°F to +130°F

Compliance

ANSI Z359.18-2017 Type A/T / Z359.7 OSHA 1926.502

Note: Use of "qualified and competent person*" in this manual: consult OSHA definition.

Non-Specified Use: Do not proof load, use for HLL or Window Washing, D-Plates

No.1038/1303/1037P

ENGLISH VERSION

!WARNING TO USER!

Fig.1



No. 1037 **HDG** Coating No. 1090 Cast Loop Top 1-3/8" i.d. MBS 15,000lb



No. 1037-P Pass-Thru 1091 Top **HLL** intermediate anchor to support cable. **DO NOT use for PPE** Tie-off

Fig.3

Note: Pass-Thru anchors are not used with 30° angle fixed

Fig.4

No. 1301 CAL-OSHA 2.0" i.d. Cast Loop Top MBS 20,000lb



length horizontal lifelines.

Specified Use:

PPE Anchor: 1 person max. user wt. 340lb including tools and equipment. Use for an anchorage connector designed to support a suspended component/tie-back line or an active fall protection system with a maximum free fall exposure of 6ft(1.8m). Users are required to wear current ANSI, CSA or OSHA compliant PPE including a personal energy absorber with a max. fall arrest force of 1,800lb. with the use of this anchor.

PPE Equipment: Users are required to use PPE that comply with current ANSI, OSHA or CSA standards including a full body harness (FBH), and personal energy absorber with a max. arrest force of 1,800lb.

SRL's: Self retracting lifelines must be equipped with an internal or external energy absorber. Horizontal Lifeline (HLL): Use with SAS pre-engineered, 30° angle fixed length Horizontal Lifelines cables No.1335. See page 4. Table 2.

Hoisting or Lifting: Consult D-Plate Hoisting Addendum 1.

Compatible Connectors

Connect PPE equipment with 3,600lb gate strength snaphooks and carabiners. Do not attach more than 1 connector to the loop top. Ensure connectors are compatible before use.

Attachment Bolt Specifications

Install with 2 or 4 bolts as specified in this manual with certified 1/2"-13 grade 8, 18-8sst bolts or A-307 threaded rod. See Fig.9 for instructions to calculate attachment bolt lengths. Bolt threads must extend 1/8" past the lock nut.

Anchor Locations

Unless specified with a Job Specific Plan, the max. spacing between anchors is 8ft. HLL spacing between anchors is 10-20ft with 2ft increments shown at Table 2.

Structural Support

The anchor attachment point must be structurally capable of supporting 5,000lb or 2x the intended fall protection load per OSHA 1910.140(13), 3rd party structural engineering is available from SAS upon request. For example: 1 person w/energy absorber maximum arrest force of 1800lb x 2= 3,600lb attachment point.

Inspections/Maintenance

Inspected before and after installation to confirm anchors are free of defects. A record of annual inspections by a competent person should be maintained. SAS inspection points may be used as part of the user and building owner's maintenance plan.

D-Plate Inspection Points

- Confirm attachment bolts comply with specifications, and are tightened with lock nuts. • PID labels must be intact.
- Inspect welds and loop tops for cracks.
- · Inspect Loop Top for deformation.

Warning! Anchors subjected to a free fall or other damage must be tagged to prevent further use until inspected by a qualified person. Remove from service if inspection does not pass and dispose of in a way that will prevent further use.

Table 1 Use Specifications

Table 1 use specifications						
Use	Part	Top Fixture		Base	Type of	See
Rating	No.	No.	Туре	Plate	Coating	Fig.
PPE	1038	Forged D-Ring		Q235 Steel	Red Powder	1
	1028				HDG	5
HLL	1037-PG	1091	Q235	Sieei	пра	3
Pass-Thru	1037-PS	1091S	316sst	304sst	N/A	
WW	1037	1090	Q235	Q235	HDG	2
PPE	1037S	1090S	316sst	304sst	N/A	
SRL	1301G	1093	Q345	Q345	HDG	4
HLL End	1301S	1093S	316sst	304sst	N/A	

PID Labels

Inspection




Fig.5



• If rust is present, re-coat w/zinc spray

D-Plate 2021 Manual English Version Page 2

Installation Examples

D-Plate anchors are installed by bolting, field welding, concrete embedment and wedge bolt. DO NOT use screws or fasteners not specified in this manual. The loop top orientation should be in the direction of the service load and may be installed skewed when used for single person PPE. Where specified, anchors may be attached with a 2-bolt pattern*.

*D-Plate anchors used as HLL end anchors require a 4-bolt pattern.

Fig.6

Min. 3/4" Plywood Substrate

Center base plate over top chord and attach with 4-bolt pattern only. DO NOT install onto OSB.




Fig.7

OSB/Plywood Substrates

OSB of any thickness and plywood less than 3/4": install using 2-bolt pattern with base and backer plates centered over the top chord.





Fig.8

Bolt-Thru Wood Beams/Glu-Lams


Install onto the top, side or bottom of the beam w/2 bolts. For narrow beams, the base plate may be installed skewed.



Loop Top Orientation

Loop tops should be oriented in the direction of the service load.

> 4-Bolt Pattern Vertical Orientation















Fig.10

Wood Screws/Lag Bolts

Requires 4-bolt pattern. Flat washers are required for WS and 7/16" lag bolts. Lag bolts require full depth pilot holes.






Field Welded to Structural Steel

Welding must be performed by a certified welder and inspected by a qualified person* prior to use. 6x6 D-Plates require a min. weld length of 5" for sides A or sides B for a 10" total weld length. Narrow flange beams less than 5" wide will require Top and underside welds to =10" total length. See example 11.1.

Wide Flange Beam 5.0" Weld (Sides A or B) **Fig.11**







Fig.9

Bolt Length Calculation

Example: add 1-1/2" to the "X" substrate thickness. Add 1/8" for flat washers.




D-Plate 2021 Manual **English Version** Page 3


Fig.12 1/2" Hex Head Bolt Top Flange Lock Nut Web

Structural Steel Bolt Attached

Bolt holes should be a min. of 1.0" from any edge. Center base plate over beam web and attach to top or bottom flange or web. Consult project engineer before drilling bolt holes.



Concrete Installations





Model 1037 shown use for Single Person PPE only.

Fig.13.1 2 or 4-Bolt Pattern Lock Nut No. 1039 Backer Plate

Concrete Specifications

Embedment or wedge bolt installations require a min. 2500 psi and a slab thickness of 4.0". Concrete must be cured sufficiently to support the fall protection load prior to use.

Bolt-Thru w/Backer Plate

- Slab thickness less than 4.0"
- · HLL end anchors require 4-bolt attachment.

Install with No.1039 backer plate


2-Bolt Installations/Vertical Walls

Any model D-Plate may be installed with the loop top orientation horizontal, skewed or vertical as shown at Fig.13.2. Use only for single person PPE. Not rated for window washing or HLL end anchors. Skewed installation provides a higher degree of waterproofing by eliminating a horizontal edge and does not affect the use of PPE connectors. Waterproofing: apply project specified caulking to all edges of the base and backer plate.

CMU Block Walls

Install D-plates for fall protection or façade structural support using thru-bolt as shown at Fig.14.2 or J-bolt embedment. Installations for 2 or 4-bolt pattern require project specific engineering with rebar and grout. Grout filling must be sufficiently cured to support the intended load prior to use. Anchors may be centered over the block cavity as shown at Fig.14 or over the center web shown at Fig.14.1. Block example is 8x8x16.

Fig.14



4-Bolt Vertical 4-Bolt Horizontal Loop Top Orientation


Fig.14.1



Loop Top orientation should be parallel with the direction of the load.

Retro-Fit Existing Walls

Existing CMU walls that are structurally capable of supporting anchorage devices can be retro-fitted using thru-bolts with backer plates. Rebar and grout not shown in the example.



No. 1039 Backer Plate

SUPER ANCHOR SAFETY®

Type B Metal Decking

Requires a 4-bolt pattern installation. Center bolt holes over top flute. Install w/flat washers and lock nuts. Use any model 6x6 D-plate anchor.




Fig.15.1 No. 1037 D-Plate Shown Vertical Orientation Slope



Horizontal Lifeline Systems (HLLS) w/D-Plate Anchors

The number of workers attached to a single or multiple leg HLL without a Job Specific Plan(JSP) are specified in Tables 3 and 4 and are based on SAS pre-engineered cable lengths. User specifications may be varied when engineered by a qualified or competent person* using SAS components.

Temporary Installations

The HLL examples shown here are intended for temporary use only and must be installed perpendicular to the slope. End anchors must be a min. of 6ft from any gable, eave edge or fall hazard. Consult SAS D-Plate HLL Rigging manual for permanent installation specifications.




Fig.18 Multiple Leg HLL




Fig.19

Permanent HLLS

Consult SAS D-Plate Rigging Manual and D-Plate2 Manual for permanent HLLS specifications.

Permanent HLL's are engineered with integral metallic energy absorbers, turnbuckles and Pass-Thru anchors. Example:

