


# Modo X III Modo New III




Modo X



Modo New



The product in the Black colour variant can be found on p. 49.




There is possibility to buy fixed SW side walls.



Modo New III + shower board

Profile finish:



01 Chrome 54 Black

Shower enclosure set consists of 3 parts: 2 models type II and 1 connector of support bars

| Model                          | Modo X II<br>transparent glass – 10 mm |                                  | Modo New II<br>transparent glass – 8 mm |                                  |
|--------------------------------|--|----------------------------------|---|----------------------------------|
|                                | profile finish CHROME<br>Art. No.      | profile finish BLACK<br>Art. No. | profile finish CHROME<br>Art. No.       | profile finish BLACK<br>Art. No. |
| Modo (X/New) II 50             | 389254-01-01                           | 389254-54-01                     | 389054-01-01                            | 389054-54-01                     |
| Modo (X/New) II 55             | 389255-01-01                           | 389255-54-01                     | 389055-01-01                            | 389055-54-01                     |
| Modo (X/New) II 60             | 389264-01-01                           | 389264-54-01                     | 389064-01-01                            | 389064-54-01                     |
| Modo (X/New) II 65             | 389265-01-01                           | 389265-54-01                     | 389065-01-01                            | 389065-54-01                     |
| Modo (X/New) II 70             | 389274-01-01                           | 389274-54-01                     | 389074-01-01                            | 389074-54-01                     |
| Modo (X/New) II 75             | 389275-01-01                           | 389275-54-01                     | 389075-01-01                            | 389075-54-01                     |
| Modo (X/New) II 80             | 389284-01-01                           | 389284-54-01                     | 389084-01-01                            | 389084-54-01                     |
| Modo (X/New) II 85             | 389285-01-01                           | 389285-54-01                     | 389085-01-01                            | 389085-54-01                     |
| Modo (X/New) II 90             | 389294-01-01                           | 389294-54-01                     | 389094-01-01                            | 389094-54-01                     |
| Modo (X/New) II 95             | 389295-01-01                           | 389295-54-01                     | 389095-01-01                            | 389095-54-01                     |
| Modo (X/New) II 100            | 389304-01-01                           | 389304-54-01                     | 389104-01-01                            | 389104-54-01                     |
| Modo (X/New) II 105            | 389305-01-01                           | 389305-54-01                     | 389105-01-01                            | 389105-54-01                     |
| Modo (X/New) II 110            | 389314-01-01                           | 389314-54-01                     | 389114-01-01                            | 389114-54-01                     |
| Modo (X/New) II 115            | 389315-01-01                           | 389315-54-01                     | 389115-01-01                            | 389115-54-01                     |
| Modo (X/New) II 120            | 389324-01-01                           | 389324-54-01                     | 389124-01-01                            | 389124-54-01                     |
| Modo (X/New) II 125            | 389325-01-01                           | 389325-54-01                     | 389125-01-01                            | 389125-54-01                     |
| Modo (X/New) II 130            | 389334-01-01                           | 389334-54-01                     | 389134-01-01                            | 389134-54-01                     |
| Modo (X/New) II 135            | 389335-01-01                           | 389335-54-01                     | 389135-01-01                            | 389135-54-01                     |
| Modo (X/New) II 140            | 389344-01-01                           | 389344-54-01                     | 389144-01-01                            | 389144-54-01                     |
| Modo (X/New) II 145            | 389345-01-01                           | 389345-54-01                     | 389145-01-01                            | 389145-54-01                     |
| Modo (X/New) II 150            | 389354-01-01                           | 389354-54-01                     | 389154-01-01                            | 389154-54-01                     |
| Modo (X/New) II 155            | 389355-01-01                           | 389355-54-01                     | 389155-01-01                            | 389155-54-01                     |
| Modo (X/New) II 160            | 389364-01-01                           | 389364-54-01                     | 389164-01-01                            | 389164-54-01                     |
| Modo (X/New) II 30-100x150-200 | 389403-01-01                           | 389403-54-01                     | 389903-01-01                            | 389903-54-01                     |
| Modo New II 30-100x200-230     | -                                      | -                                | 389904-01-01                            | 389904-54-01                     |
| Modo X II 30-100x200-250       | 389404-01-01                           | 389404-54-01                     | -                                       | -                                |
| Modo X II 30-100x250-300       | 389405-01-01                           | 389405-54-01                     | -                                       | -                                |
| Modo New II 100-140x150-200    | -                                      | -                                | 389905-01-01                            | 389905-54-01                     |
| Modo New II 100-140x200-230    | -                                      | -                                | 389906-01-01                            | 389906-54-01                     |
| Modo X II 100-160x150-200      | 389407-01-01                           | 389407-54-01                     | -                                       | -                                |
| Modo X II 100-160x200-250      | 389408-01-01                           | 389408-54-01                     | -                                       | -                                |
| Modo X II 100-160x250-300      | 389409-01-01                           | 389409-54-01                     | -                                       | -                                |
| Modo New II 140-180x150-200    | -                                      | -                                | 389907-01-01                            | 389907-54-01                     |
| Modo New II 140-180x200-230    | -                                      | -                                | 389908-01-01                            | 389908-54-01                     |

## CONNECTOR OF SUPPORT BARS

| Model                     | Art. No.  |           |
|---------------------------|-----------|-----------|
|                           | Chrome    | Black     |
| Connector of support bars | 389000-01 | 389000-54 |

It is possible to order the width of the Sidewall 2 > 125. This option should be clearly stated in the order. It is possible to order the shower enclosure in the Frame or Factory variant (with transparent, satin, bronze, graphite, Mirror or UltraClear® glass).




Modo X Black III Frame  
Modo New Black III Frame



Modo X Black III Factory  
Modo New Black III Factory

Catalogue sheets are available at [radaway.eu](http://radaway.eu)

## TECHNICAL DRAWINGS




It is possible to create a shower enclosure m with a fixed, L-shaped sidewall SW 300 mm wide. It can be matched with 8mm glass only. In this case, when ordering, please also specify the sidewall index number: chrome - 388000-01-01, black - 388000-54-01.

| Sidewall 1          | X1       | X2       | E         | H    |
|---------------------|----------|----------|-----------|------|
| Modo (X/New) II 50  | max 1700 | max 1200 | 485-495   | 2000 |
| Modo (X/New) II 55  | max 1750 | max 1200 | 535-545   | 2000 |
| Modo (X/New) II 60  | max 1800 | max 1200 | 585-595   | 2000 |
| Modo (X/New) II 65  | max 1850 | max 1200 | 635-645   | 2000 |
| Modo (X/New) II 70  | max 1900 | max 1200 | 685-695   | 2000 |
| Modo (X/New) II 75  | max 1950 | max 1200 | 735-745   | 2000 |
| Modo (X/New) II 80  | max 2000 | max 1200 | 785-795   | 2000 |
| Modo (X/New) II 85  | max 2050 | max 1200 | 835-845   | 2000 |
| Modo (X/New) II 90  | max 2100 | max 1200 | 885-895   | 2000 |
| Modo (X/New) II 95  | max 2150 | max 1200 | 935-945   | 2000 |
| Modo (X/New) II 100 | max 2200 | max 1200 | 985-995   | 2000 |
| Modo (X/New) II 105 | max 2250 | max 1200 | 1035-1045 | 2000 |
| Modo (X/New) II 110 | max 2300 | max 1200 | 1085-1095 | 2000 |
| Modo (X/New) II 115 | max 2350 | max 1200 | 1135-1145 | 2000 |
| Modo (X/New) II 120 | max 2400 | max 1200 | 1185-1195 | 2000 |
| Modo (X/New) II 125 | max 2450 | max 1200 | 1235-1245 | 2000 |
| Modo (X/New) II 130 | max 2500 | max 1200 | 1285-1295 | 2000 |
| Modo (X/New) II 135 | max 2550 | max 1200 | 1335-1345 | 2000 |
| Modo (X/New) II 140 | max 2600 | max 1200 | 1385-1395 | 2000 |
| Modo (X/New) II 145 | max 2650 | max 1200 | 1435-1445 | 2000 |
| Modo (X/New) II 150 | max 2700 | max 1200 | 1485-1495 | 2000 |
| Modo (X/New) II 155 | max 2750 | max 1200 | 1535-1545 | 2000 |
| Modo (X/New) II 160 | max 2800 | max 1200 | 1585-1595 | 2000 |

| Sidewall 2          | X3        | D        |
|---------------------|-----------|----------|
| Modo (X/New) II 50  | 485-495   | max 1200 |
| Modo (X/New) II 55  | 535-545   | max 1200 |
| Modo (X/New) II 60  | 585-595   | max 1200 |
| Modo (X/New) II 65  | 635-645   | max 1200 |
| Modo (X/New) II 70  | 685-695   | max 1200 |
| Modo (X/New) II 75  | 735-745   | max 1200 |
| Modo (X/New) II 80  | 785-795   | max 1200 |
| Modo (X/New) II 85  | 835-845   | max 1200 |
| Modo (X/New) II 90  | 885-895   | max 1200 |
| Modo (X/New) II 95  | 935-945   | max 1200 |
| Modo (X/New) II 100 | 985-995   | max 1200 |
| Modo (X/New) II 105 | 1035-1045 | max 1200 |
| Modo (X/New) II 110 | 1085-1095 | max 1200 |
| Modo (X/New) II 115 | 1135-1145 | max 1200 |
| Modo (X/New) II 120 | 1185-1195 | max 1200 |

It is possible to order the width of the Sidewall 2 > 125. This option should be clearly stated in the order.

## ADDITIONAL OPTIONS



| Telescopic support bar | For glass | Height      | Colour | Art. No.     |
|------------------------|-----------|-------------|--------|--------------|
|                        | 8 mm      | max 3000 mm |        | WD-008-02    |
|                        |           |             |        | WD-008-02-54 |

## NAVIGATION

