

Image Intensifier specification  
18 millimetre micro-channel wafer  
**ECHO**  
**ZW1059A**



184-7380A0

Page 1 of 2

## Description

The Image Intensifier Assembly, 18 millimetres micro-channel wafer, shall have a minimum useful photocathode and phosphor screen diameter of 17.0 millimetres (mm). The assembly shall employ a micro-channel electron multiplier plate with proximity focus on the input and output. The assembly shall include the high voltage multiplier and oscillator and shall be encapsulated within a hard surface insulating sleeve or boot and assembled in a hard plastic housing. The tube is equipped with **AUTO-GATING**

Phosphor : P45  
Input window : Glass  
Output window : Non-Inverting fibre-optic

## Construction

The assembly shall be fabricated in accordance with the applicable drawing 183-1059A\*.

## Limiting values

	<u>Minimal</u>	<u>Maximal</u>	<u>Unit</u>
Continuous input Supply voltage	2.0	3.5	V
Reversed Polarity (60 sec)	-3.7	+3.7	V
Storage temperature long term	-35	+35	°C
Operating temperature (4 hours max.)	-33	+49	°C
Force on bearing surface		200	N

## Operating conditions and characteristics

Operating Supply voltage : 2.7 V  
Ambient temperature : 20 ± 1°C

When the image intensifier is operated under the conditions mentioned above, unless otherwise specified, the characteristic values that follow are attainable:

Date  
March 15, 2018

Signed  
BJE

Checked  
OR

184-7380A0

Image Intensifier specification  
 18 millimetre micro-channel wafer  
**ECHO**  
**ZW1059A**



184-7380A0

Page 2 of 2

Property of the Photonis Group.  
 Reproduction, or disclosure to third parties,  
 in any form whatsoever not allowed without  
 written consent of Photonis.

Propriété du groupe Photonis.  
 La reproduction ou la diffusion à une tierce partie, sous  
 quelque forme que ce soit, sans accord écrit de Photonis, est  
 strictement interdite.

Eigendom van de Photonis Groep.  
 Vermenigvuldigen of mededeling aan derden, in welke vorm  
 ook is zonder schriftelijke toestemming van Photonis niet  
 geoorloofd.

	Minimal	Typical	Maximal	UNIT
FOM	1500		1800	
Signal to noise ratio (Photocathode illuminance 108 $\mu$ lx)	24			
Gain at $2.10^{-5}$ lx	8000		12000	cd/m <sup>2</sup> /lx
Gain at $2.10^{-6}$ fc	(25120)		(37680)	fL/fc
Maximum Output Brightness	4		8	cd/m <sup>2</sup>
Maximum Output Brightness	(1.2)		(2.3)	fL
Input current at $2.10^{-5}$ lx			35	mA
Limiting resolution at centre	57		74	lp/mm
Limiting resolution at >200 lux (=autogating mode)	50			lp/mm
Burn-in	50			hours
Shear distortion			50	$\mu$ m
Gross distortion			50	$\mu$ m
Useful cathode diameter	17.0			mm
Halo (illumination spot 0.35mm)			0.95	mm

### Spots:

Maximum number of dark spots will be according to the following table:

SPOTS DIAMETER IN MICROMETERS	ZONE 1 dia. 5.6mm	ZONE 2 dia. 5.6mm-14.7mm	ZONE 3 dia 14.7mm-17.0mm
➤ 300	0	0	0
230 – 300	0	1	2
150 – 230	1	2	4
75 – 150	2	4	6

In case the assembly has more numerous dark spots of smaller dimension within a zone, the total quantity of dark spots in the zone should be within the total quantity of dark spots in the considered zone as specified in the above table.

For example, if a tube is showing [5 Ø75-150 $\mu$ m] dark spots in zone 2 instead of the [4 Ø75-150 $\mu$ m + 2 Ø150-230 $\mu$ m] specified ones, the tube will be considered to be compliant with the specification.

Date  
 March 15, 2018

Signed  
 BJE

Checked  
 OR

184-7380A0